

HBL5965VBLK -- Valise Plug



2P3W, 15A 125V, 5-15P, Black Nylon


Product Specifications

Product Type	 Plugs
Body Style	Straight
Standard	NEMA
Amperage	15A
Voltage	125V
Poles and Wires	2 Pole, 3 Wire Grounding
Hospital Grade ?	No
Plug/Connector Grade	Valise
Color	 Black
NEMA No.	5-15P
Horsepower	0.5

Cord Dia.	.220"-.660" (5.6-16.8)
Description	Straight Blade Plug
Type	2 Pole, 3 Wire, Grounding
Rating	15A,125V
Certification	UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280
IP Suitability	IP20
Housing Material	Nylon
Cord Clamp Material	Noryl (Polyphenylene Oxide)
Contact Blades Material	.060" (1.5) Brass
Ground Contact Blade Material	.040" (1.0) Brass
Terminal Screw Material	Steel (copper or nickel finish)
Ground Screw Material	Steel (green finish)
Wire Clamps Material	.062" (1.8) Steel-nickel finish
Cable Inserts Material	Poly Phenylene Oxide
Body Holding Screws	Steel Multiple Drive
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).
Terminal Accommodation	#18-#10 AWG copper stranded conductor
Product Identification	Ratings are a permanent part of the device.
Flammability	UL 94 V2.
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).
M Drawings	Click here for M-Drawing
Catalog Page	Click here for catalog page A22
Brochures	Click here for product brochure
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-A
UPC Number	78358501308

Weight in LBs

0.15



Hubbell Incorporated (Delaware)
185 Plains Road
Milford, CT 06460-2420
Ph: (203) 882-4800
Fax: (800) 255-1031



Wiring Device-Kellems