

*Think Automation and beyond...*



**LUMIFA™**

# LF1D/LF2D Series LED Illumination Units

Brightest in its class, great power savings!

The unique lens design, optimized power circuit, and heat dissipation structure achieves high brightness both at the center and periphery.



IDEC CORPORATION


Illumination for industrial purposes are required to guarantee resistance against harsh environments subject to water, oil, and metal chips, while providing brightness specified by standards. IDEC's LUMIFA LED Illumination units ensure long service life, energy savings, low heat generation, cleanliness and high resistance against shock. The LUMIFA series achieves high environment resistance and brightness required to ensure safety in working environments. The slim profile design of the highly bright LED modules and efficient heat dissipation technology is ideal for installation in various machines and equipment.

## LF1D/LF2D Series LED Illumination Units

Brightest in its class, excellent power savings. The optimal optical design achieves high brightness both at both the center and edges. IP67f degree of protection.



### Robust and Resistant



- Degree of protection IP67f (reinforced glass illumination surface). Waterproof, dust-proof, and oil-proof. Can be used in environments subject to water, dust, and oil.
- Construction of diecast aluminum (base), stainless steel (front), and reinforced glass. Resistant against flying chips.

Note 1: Polycarbonate available for applications such as food machines.

Note 2: LF2D is in aluminum diecast.

### High Brightness, Energy Savings, and Compact Size!

#### • Brightest in its class

The optimal optical design achieves high brightness. Achieves illuminance specified by EN1837: 1999, 4.2. (1100 lx at 1m directly below)

#### • Heat Dissipation

Heat is dissipated by the aluminum housing efficiently.



#### • Efficient power circuit

Highly efficient, low-heat power circuit.




#### • Glare prevention

Diffused type available to prevent glaring light and reflection. (EN1837: 1999, 4.3.)



### Optimal Light Distribution

#### • Distribution Characteristics (reference value at 1.0m)




## LF series LED Illumination Units

|                             |                                                                                                         |
|-----------------------------|---------------------------------------------------------------------------------------------------------|
| Low heat:                   | LED illumination generate very little heat, unlike incandescent and halogen lamps.                      |
| Long service life:          | Maintenance-free operation for 50,000 hours.                                                            |
| Vibration/shock resistance: | Highly resistant.                                                                                       |
| Energy saving:              | Less power consumption when compared with fluorescent lamps, contributing to CO <sub>2</sub> reduction. |
| RoHS compliant:             | Environmentally friendly compared with mercury-laden fluorescent lamps.                                 |


## Easy Maintenance

### • Spring-clamp terminal blocks


Removable direct plug-in terminal block and spring clamp connections ensure a high quality connection, making it easy to install or replace the LED illumination unit.




### <Connection Example>




## Accessories



Cable gland, cable, and mounting brackets are also available as accessories for installation in various applications.



Screw holes are provided on the sides for installation using mounting brackets, and also on the back for direct mounting. Cable can be connected from the rear.



## Applications

### LF1D

An application in a drilling machine.



### LF2D—slim flange design.

Only 5 mm extension from the mounting panel.



Flush mounting of LF2D minimizes the build-up of metal chips.



# LUMIFA™ LF1D/LF2D LED Illumination Units

**Brightest in its class, excellent power savings. Optimal optical design achieves high brightness at both the center and periphery. IP67f degree of protection.**

- LED provides energy-savings, long-life, space-saving and no-maintenance advantages.
- Illumination surface variety—reinforced glass or polycarbonate, both in clear or diffused type.
- IP67f degree of protection (polycarbonate: IP67)
- Robust housing of aluminum diecast and stainless steel.
- Thin and slim profiles allow installation in space-limited areas.
- Even low profile is available with the sleek design of LF2D. Resistant to dust build up on the surface.

## Application examples

Machine tools, food processing equipment, automatic manufacturing machines, printing machines, production system, test equipment, refrigeration and freezers.



UL, c-UL listed: LF1D only



## Types

### • LF1D (Illumination color: white)

| Type                                           |                |                                 | Slim Type (LF1D-E)     |                     | Wide Type (LF1D-F)     |                     |
|------------------------------------------------|----------------|---------------------------------|------------------------|---------------------|------------------------|---------------------|
| Appearance                                     |                |                                 |                        |                     |                        |                     |
| LED Arrangement                                |                |                                 | 10 LEDs × 1 row        |                     | 7 LEDs × 2 rows        |                     |
| Optional Accessories                           |                |                                 | Illumination Surface   |                     | Illumination Surface   |                     |
| Cable Gland LF9Z-A11                           | Cable LF9Z-C05 | Mounting Bracket LF9Z-B11, -B12 | Clear Reinforced Glass | Clear Polycarbonate | Clear Reinforced Glass | Clear Polycarbonate |
| Without (Cable gland hole on the side of LF1D) | —              | —                               | LF1D-E2F-2W            | LF1D-E3G-2W         | LF1D-F2F-2W            | LF1D-F3G-2W         |
|                                                |                | With                            | LF1D-E2F-2W-101        | LF1D-E3G-2W-101     | LF1D-F2F-2W-101        | LF1D-F3G-2W-101     |
| Without (Cable gland hole on the back of LF1D) | —              | —                               | LF1D-E2F-2W-200        | LF1D-E3G-2W-200     | LF1D-F2F-2W-200        | LF1D-F3G-2W-200     |
|                                                |                | With                            | LF1D-E2F-2W-201        | LF1D-E3G-2W-201     | LF1D-F2F-2W-201        | LF1D-F3G-2W-201     |
| With (Side)                                    | —              | —                               | LF1D-E2F-2W-300        | LF1D-E3G-2W-300     | LF1D-F2F-2W-300        | LF1D-F3G-2W-300     |
|                                                |                | With                            | LF1D-E2F-2W-301        | LF1D-E3G-2W-301     | LF1D-F2F-2W-301        | LF1D-F3G-2W-301     |
|                                                | With           | —                               | LF1D-E2F-2W-350        | LF1D-E3G-2W-350     | LF1D-F2F-2W-350        | LF1D-F3G-2W-350     |
|                                                |                | With                            | LF1D-E2F-2W-A          | LF1D-E3G-2W-A       | LF1D-F2F-2W-A          | LF1D-F3G-2W-A       |
| With (Back)                                    | —              | —                               | LF1D-E2F-2W-400        | LF1D-E3G-2W-400     | LF1D-F2F-2W-400        | LF1D-F3G-2W-400     |
|                                                |                | With                            | LF1D-E2F-2W-401        | LF1D-E3G-2W-401     | LF1D-F2F-2W-401        | LF1D-F3G-2W-401     |
|                                                | With           | —                               | LF1D-E2F-2W-450        | LF1D-E3G-2W-450     | LF1D-F2F-2W-450        | LF1D-F3G-2W-450     |
|                                                |                | With                            | LF1D-E2F-2W-451        | LF1D-E3G-2W-451     | LF1D-F2F-2W-451        | LF1D-F3G-2W-451     |

• Contact IDEC for cable gland hole other than the standard M8 size.

### • LF2D (Illumination color: white)

| Type                                           |                |                                 | Slim Type (LF2D-E)     |                     | Wide Type (LF2D-F)     |                     |
|------------------------------------------------|----------------|---------------------------------|------------------------|---------------------|------------------------|---------------------|
| Appearance                                     |                |                                 |                        |                     |                        |                     |
| LED Arrangement                                |                |                                 | 10 LEDs × 1 row        |                     | 7 LEDs × 2 rows        |                     |
| Optional Accessories                           |                |                                 | Illumination Surface   |                     | Illumination Surface   |                     |
| Cable Gland LF9Z-A11                           | Cable LF9Z-C05 | Mounting Bracket LF9Z-B11, -B12 | Clear Reinforced Glass | Clear Polycarbonate | Clear Reinforced Glass | Clear Polycarbonate |
| Without (cable gland hole on the side of LF2D) | —              | —                               | LF2D-E2F-2W            | LF2D-E3G-2W         | LF2D-F2F-2W            | LF2D-F3G-2W         |
|                                                |                | With                            | LF2D-E2F-2W-101        | LF2D-E3G-2W-101     | LF2D-F2F-2W-101        | LF2D-F3G-2W-101     |
| Without (cable gland hole on the back of LF2D) | —              | —                               | LF2D-E2F-2W-200        | LF2D-E3G-2W-200     | LF2D-F2F-2W-200        | LF2D-F3G-2W-200     |
|                                                |                | With                            | LF2D-E2F-2W-201        | LF2D-E3G-2W-201     | LF2D-F2F-2W-201        | LF2D-F3G-2W-201     |
| With (Side)                                    | —              | —                               | LF2D-E2F-2W-300        | LF2D-E3G-2W-300     | LF2D-F2F-2W-300        | LF2D-F3G-2W-300     |
|                                                |                | With                            | LF2D-E2F-2W-A          | LF2D-E3G-2W-A       | LF2D-F2F-2W-A          | LF2D-F3G-2W-A       |
| With (Back)                                    | —              | —                               | LF2D-E2F-2W-400        | LF2D-E3G-2W-400     | LF2D-F2F-2W-400        | LF2D-F3G-2W-400     |
|                                                |                | With                            | LF2D-E2F-2W-450        | LF2D-E3G-2W-450     | LF2D-F2F-2W-450        | LF2D-F3G-2W-450     |

• Contact IDEC for cable gland hole other than the standard M8 size.

## Accessories

| Type             | Material        | Type No. | Remarks                                  | Package Quantity |
|------------------|-----------------|----------|------------------------------------------|------------------|
| Cable Gland      | Brass           | LF9Z-A11 | M8, applicable wire size: ø3.5 to 5.5 mm | 1                |
| Mounting Bracket | Stainless Steel | LF9Z-B11 | With mounting screws                     | 2                |
|                  |                 | LF9Z-B12 | With mounting screws                     | 2                |
| Cable            | PVC             | LF9Z-C05 | 5m                                       | 1                |


• Contact IDEC for angle adjustable mounting bracket (LF1D).




## Dimensions

All dimensions in mm.


- **LF1D-E (Slim Type, 10 LEDs × 1 row)**




- **Mounting Hole Layout**



- **LF1D-F (Wide Type, 7 LEDs × 2 rows)**




- **Mounting Hole Layout**




# LUMIFA™ LF1D/LF2D LED Illumination Units

## Dimensions


### • LF2D-E (Slim Type, 10 LEDs × 1 row)




### • Mounting Hole Layout



### • LF2D-F (Wide Type, 7 LEDs × 2 rows)



### • Mounting Hole Layout



## Safety Precautions

- Do not disassemble, repair, or modify illumination units. Otherwise electric shock, fire, or malfunction may occur.
- Turn off power to the illumination units before wiring. Make sure of correct wiring, otherwise electric shock or damage may result.
- Do not stare directly into the illumination unit while it is lit, and do not project the light to other people, otherwise eyes may be injured.
- The illumination unit is a general-purpose industrial electric device. Do not use the illumination unit for electronic equipment which may damage the human body or threaten life in case a malfunction or failure occurs.

## Instructions

- Before designing final equipment and powering up illumination units, confirm the specifications described on the instruction sheet. If there is any uncertainty, contact IDEC before powering up illumination units.
- Apply voltage within the rated value, otherwise the LED elements may be damaged.
- The illumination unit is vulnerable to static electricity. Take sufficient measure for protection against static electricity and voltage surges.
- Make sure that the illumination unit does not fall during transportation, installation, and operation, otherwise damage may result.
- Do not pull or push the cable of the illumination unit, otherwise damage may result. Allow sufficient slack to the cable while wiring.
- Do not apply excessive force to the illumination unit. Do not leave a damaged illumination unit unattended or use a damaged illumination unit.
- Ensure the correct operating temperature around the illumination unit. Otherwise internal temperature rise may result in damage.
- Do not use or store the illumination unit in a place subjected to vibration and shock.
- Do not use the illumination unit in the following places:
  - \* Exposed to direct sunlight, near heaters, and at high temperatures
  - \* Subject to chemicals, and corrosive gases (Plastic illumination surface types: Iron powder and oil)
  - \* Basements, greenhouses, or other humid places
  - \* Cold storage warehouses and cooler exhaust outlets (make sure that no freezing occurs)
- Do not loosen screws, otherwise the protection characteristics will be impaired.
- For the LF2D illumination units, make sure to provide sufficient strength for mounting panel. Required waterproof characteristics cannot be obtained if a distorted mounting panel is used.
- Use illumination units with a Class 2 power supply.

Specifications and other descriptions in this catalog are subject to change without notice.



## IDEC CORPORATION

7-31, Nishi-Miyahara 1-Chome, Yodogawa-ku, Osaka 532-8550, Japan  
Tel: +81-6-6398-2571, Fax: +81-6-6392-9731  
E-mail: marketing@idec.co.jp

**IDEC CORPORATION (USA)**  
1175 Elko Drive, Sunnyvale, CA 94089-2209, USA  
Tel: +1-408-747-0550 / (800) 262-IDEC (4332)  
Fax: +1-408-744-9055 / (800) 635-6246  
E-mail: opencontact@idec.com

**IDEC CANADA LIMITED**  
3155 Pepper Mill Court, Unit 4, Mississauga,  
Ontario, L5L 4X7, Canada  
Tel: +1-905-890-8561, Toll Free: (888) 317-4332  
Fax: +1-905-890-8562  
E-mail: sales@ca.idec.com

**IDEC AUSTRALIA PTY. LTD.**  
2/3 Macro Court, Rowville, Victoria 3178, Australia  
Tel: +61-3-9763-3244, Toll Free: 1800-68-4332  
Fax: +61-3-9763-3255  
E-mail: sales@au.idec.com

**IDEC ELECTRONICS LIMITED**  
Unit 2, Beechwood, Chineham Business Park,  
Basingstoke, Hampshire RG24 8WA, UK  
Tel: +44-1256-321000, Fax: +44-1256-327755  
E-mail: sales@uk.idec.com

**IDEC ELEKTROTECHNIK GmbH**  
Wendenstrasse 331, 20537 Hamburg, Germany  
Tel: +49-40-25 30 54 - 0, Fax: +49-40-25 30 54 - 24  
E-mail: service@idec.de

**IDEC (SHANGHAI) CORPORATION**  
Room 608-609, 6F, Gangtai Plaza, No. 700,  
Yan'an East Road, Shanghai 200001, PRC  
Tel: +86-21-5353-1000, Fax: +86-21-5353-1263  
E-mail: idec@cn.idec.com

**IDEC (BEIJING) CORPORATION**  
Room 211B, Tower B, The Grand Pacific Building,  
8A Guanghua Road, Chaoyang District,  
Beijing 100026, PRC  
Tel: +86-10-6581-6131, Fax: +86-10-6581-5119

**IDEC (SHENZHEN) CORPORATION**  
Unit AB-3B2, Tian Xiang Building, Tian'an Cyber Park,  
Fu Tian District, Shenzhen, Guangdong 518040, PRC  
Tel: +86-755-8356-2977, Fax: +86-755-8356-2944

**IDEC IZUMI (H.K.) CO., LTD.**  
Units 11-15, Level 27, Tower 1,  
Millennium City 1, 388 Kwun Tong Road,  
Kwun Tong, Kowloon, Hong Kong  
Tel: +852-2803-8989, Fax: +852-2565-0171  
E-mail: info@hk.idec.com

**IDEC TAIWAN CORPORATION**  
8F-1, No. 79, Hsin Tai Wu Road, Sec. 1,  
Hsi-Chih, Taipei County, Taiwan  
Tel: +886-2-2698-3929, Fax: +886-2-2698-3931  
E-mail: service@tw.idec.com

**IDEC IZUMI ASIA PTE. LTD.**  
No. 31, Tannery Lane #05-01,  
HB Centre 2, Singapore 347788  
Tel: +65-6746-1155, Fax: +65-6844-5995  
E-mail: info@sg.idec.com