

Features

- ◆ Smallest encapsulated 20W converter!
Ultra compact size: 1.0" x 1.0" x 0.4"
- ◆ Shielded metal case with isolated baseplate
- ◆ Ultrawide 4:1 input voltage ranges
- ◆ Very high efficiency up to 90%
- ◆ Output voltage adjustable
- ◆ Remote On/Off control
- ◆ Operating temp. range -40°C to +75°C
and up to +85°C with heat-sink
- ◆ I/O isolation voltage 1500 VDC
- ◆ Lead free design, RoHS compliant
- ◆ 3-year product warranty



The THL 20WI series is the latest generation of dc-dc converter modules with highest power density. The product achieves 20 Watt output power while it comes in a metal case with dimensions of only 1.0"x 1.0"x 0.4".

All models have an ultra wide 4:1 input voltage range and precisely regulated output voltages. Highest efficiency of up to 90% makes this product very reliable and applicable in temperature ranges of up to +75°C or +85°C with optional mounted heat sink. Typical applications are in mobile equipments, instrumentation, distributed power architectures in communication and industrial electronics and everywhere where space on the PCB is critical.

Models

Order code	Input voltage range	Output voltage	Output current max.	Efficiency typ.
THL 20-2410WI	9 – 36 VDC (24 VDC nominal)	3.3 VDC	4500 mA	89 %
THL 20-2411WI		5.0 VDC	4000 mA	90 %
THL 20-2412WI		12 VDC	1670 mA	89 %
THL 20-2413WI		15 VDC	1340 mA	89 %
THL 20-2415WI		24 VDC	835 mA	88 %
THL 20-2422WI		±12 VDC	±835 mA	89 %
THL 20-2423WI		±15 VDC	±670 mA	89 %
THL 20-4810WI	18 – 75 VDC (48 VDC nominal)	3.3 VDC	4500 mA	89 %
THL 20-4811WI		5.0 VDC	4000 mA	90 %
THL 20-4812WI		12 VDC	1670 mA	89 %
THL 20-4813WI		15 VDC	1340 mA	90 %
THL 20-4815WI		24 VDC	835 mA	88 %
THL 20-4822WI		±12 VDC	±835 mA	89 %
THL 20-4823WI		±15 VDC	±670 mA	89 %

Input Specifications

Input current at no load (at nominal input voltage)	24 V single output models: 24 V dual output models: 48 V single output models: 48 V dual output models:	80 mA typ. 40 mA typ. 40 mA typ. 25 mA typ.
Input current at full load (at nominal input voltage)	24 V; 3.3 VDC models: 24 V; other models: 48 V; 3.3 VDC models: 48 V; other models:	700 mA typ. 940 mA typ.. 350 mA typ. 470 mA typ.
Start-up voltage	24 V models: 48 V models:	9 VDC (or lower) 18 VDC (or lower)
Surge voltage (1 sec. max.)	24 Vin models: 48 Vin models:	50 V max. 100 V max.
Reflected input ripple current	24 V models: 48 V models:	50 mAp-p typ. 30 mAp-p typ.
Conducted noise (input)	EN 55022 class A, FCC part 15, level A with external components (see application note)	

Output Specifications

Voltage set accuracy	$\pm 1\%$	
Output voltage adj. range	$\pm 10\%$ for single output models only. Trim up via resistor over Trim and -Vout Trim down via resistor over Trim and +Vout (Resistor values tba, 0 Ohm=max. adjustment)	
Regulation	– Input variation (Vmin – Vmax) – Load variation	single output models: 0.2 % max. dual output models: 0.5 % max. single output models: 0.5 % max. (0 – 100 % load) dual output models: 1.0 % max. (8 – 100 % balanced load)
Minimum load	single output models: dual output models:	not required 8 % of rated max current (operation at lower load condition will not damage the converters. However, they may not meet all listed specifications)
Ripple and noise (20 MHz bandwidth)	3.3 & 5.0 VDC models: 12 & 15 VDC models: 24 VDC models:	75 mVp-p typ. 100 mVp-p typ. 150 mVp-p typ. Measured with a 1 μ F M/C and a 10 μ F T/C
Temperature coefficient	$\pm 0.02\%/K$	
Output current limitation	at 150 % of Iout max., foldback	
Short circuit protection	indefinite, automatic recovery	
Transient response setting time	300 μ s typ. (25% load step change)	
Max. capacitive load	3.3 VDC models: 5 VDC models: 12 VDC models: 15 VDC models: 24 VDC models: ± 12 VDC models: ± 15 VDC models:	10'300 μ F 6'800 μ F 1'200 μ F 750 μ F 300 μ F 680 μ F (each output) 380 μ F (each output)

General Specifications


Temperature ranges	– Operating without heat sink – Operating with heat sink – Case temperature – Storage	–40°C to +75°C (with derating) –40°C to +85°C (with derating) +105°C max. –50°C to +125°C
Power derating	– Operating without heat sink – Operating with heat sink	3.5 %/K above +65°C 3.5 %/K above +70°C
Thermal inpedance	– Natural convection – Natural convection with heat sink	18.2°C/W 15.8°C/W
Humidity (non condensing)		95 % rel H max.
Reliability, calculated MTTF (MIL-HDBK-217F, at +25°C, ground benign)		>346'000 h
Isolation voltage (60sec.)	– Input/Output	1500 VDC
Isolation capacitance	– Input/Output	1500 pF typ.
Isolation resistance	– Input/Output (500 VDC)	>1000 MOhm
Remote On/Off	– On: – Off: – Off idle current:	3.5 ... 15 VDC or open circuit 0 ... 1.2 VDC or short circuit pin 6 and pin 2 8 mA
Switching frequency (fixed)		330 kHz typ. (pulse width modulation PWM)
Safety standards		UL/cUL 60950-1, IEC/EN 60950-1
Safety approvals	– UL/cUL	www.ul.com > File no. E188913 (entry pending)
Environmental compliance	– Reach – RoHS	www.tracopower.com/products/thl20wi-reach.pdf RoHS directive 2002/95/EC

Physical Specifications

Casing material	metal
Baseplate	non conductive FR4
Potting material	epoxy (UL 94V-0 rated)
Weight	15 g (0.53 oz)
Soldering temperature	max. 260°C / 10sec.

Application note : www.tracopower.com/products/thl20wi-application.pdf

Outline Dimensions



Pin-Out

Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	Trim	Common
5	-Vout	-Vout
6	Remote On/Off	

Dimensions in [mm], () = Inch
 Pin diameter $\varnothing$ 1.0 (0.04)
 Pin pitch tolerances: ± 0.25 (± 0.01)
 Tolerances: ± 0.5 (± 0.02)

Heat-Sink (Option)

Order code: THL-HS1

(cont.: heat-sink, thermal pad, 2 clamps)

Material: Aluminum

Finish: Anodic treatment (black)




Weight: 8 g (0.28 oz) without converter

Thermal impedance after assembling: 15.8 K/W



Note:

The product label on converter has to be removed before mounting the heat-sink.
 For volume orders converters will be supplied with heat-sink already mounted. Please contact factory for quotation.
 Separate heat-sinks are only available for prototypes and small quantity orders.



Specifications can be changed any time without notice.