



This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

CUSTOMER DRAWING

ORIGINAL

REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	APPROVED
A		RELEASE FOR RoHS	08/10/2005	Henry Ko



NOTES:

- BODY: BRASS, GOLD PLATED
CONTACT: BERYLLIUM COPPER, 30μ" GOLD PLATED
INSULATION: TEFLON / NATURE
COVER: BRASS, GOLD PLATED
- CABLE: RG174U COAXIAL CABLE, COLOR- BLACK
- CONNECTOR: MMCX, R/A PLUG CONNECTOR
- SURFACE CLEANER: PDI ALCOHOL PREP PAD
- TAPER: PE FOAM
- THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS MATERIALS PER DIRECTIVE 2002/95/EC FOR RoHS.



ELECTRICAL SPEC:

- IMPEDANCE: 50 OHMS
- FREQUENCY BAND:
880 ~ 960 MHZ
1710 ~ 1880 MHZ
1900 ~ 2170 MHZ
FOR GSM 900/GSM 1800 DCS/PCS/UMTS/CDMA
- GAIN: 0 dB
- V.S.W.R.: 1.6:1 MAX.

TOLERANCE m/m	APPROVALS	DATE	TITLE	Amphenol® Amphenol Corporation Amphenol Taiwan Corporation	
x. ±0.30	DRAWN Sondra Sang	08/10/05	GSM FLAT ANTENNA	SCALE N.A.	SHEET 1 OF 1
x.x ±0.25	CHECKED <input type="checkbox"/> Laura Su	08/10/05	TRIPLE BAND, MMCX CONNECTOR		
x.xx ±0.15	APPROVED <input type="checkbox"/> Ken Lin for	08/10/05	50 OHMS		
x.xxx ±0.08					
ANGULAR ±2°					
UNLESS OTHERWISE SPECIFIED		UNIT MM	SIZE A4	PART NO. GAN 30060 EU	DRAWING NO. OTHER-GAN30060EU-29
					REV. A