





PRODUCT NUMBER
63346-XXX
63346-XXYLF




PLATING IN CONTACT AREA		
DASH NUMBER	PERFORMANCE LEVEL	NOTES
-1YY	TELCORDIA CO	-
-2YY	TELECOM CLASS	-
-3YY	IEC CLASS I	-
-5YY	TELCORDIA UE	-
-9YY	TELCORDIA CO	-
-1YYLF	TELCORDIA CO IEC CLASS I	SEE NOTE 8
-2YYLF	TELECOM CLASS	SEE NOTE 8
-5YYLF	TELCORDIA UE	SEE NOTE 8

mat'l code				--		tolerances unless otherwise specified		CUSTOMER		FCi		www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0. X ±0.3		projection		title	METRAL POWER HEADER 1 MOD, 5 ROW STB			
A	V02642	JWS	10/17/00		0. XX ±0.13								
B	V10908	CGD	02/22/01		. XXX ±.051								
C	V11897	CGD	08/27/01	angles	0° ±2°			scale	product family	METRAL		code	
D	V21671	TAB	10/21/02	dr	T.BRUNGARD	11/19/99				size	dwg no	213	
E	V05-1131	VS	02/25/06	enrg	M.STRAWSE	11/19/99							sheet
F	V06-0498	DCH	2006-05-30	chr	M.STRAWSE	11/19/99	1 of 3						
				appd	M.STRAWSE	02/29/00		2:1		A	63346		
sheet index		revision sheet		F	F	F							
				1	2	3							



PRODUCT NUMBER
63346-XXX
63346-XXYLF



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE
SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
P01	6.50	4.25
P02	7.25	4.25
P03	8.00	4.25
P04	5.00	4.25
P05	5.75	4.25

- NOTES:
- FOR DIM A AND B SEE SHEET 2 AND UP.
 - BODY MATERIAL: LIQUID CRYSTAL POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
 - PIN MATERIAL:
PHOSPHOR BRONZE.
 - PLATING ON PRESS-FIT TAIL:
63346-XXX IS SnPb
63346-XXYLF IS Sn (LEAD FREE).
PLATING ON CONTACT AREA CONFORMS
TO PERFORMANCE LEVEL SHOWN IN TABLE.
 - PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.
 - ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP OR XXXXX-XXXP.
 - PRODUCT SPECIFICATION GS-12-180.
APPLICATION SPECIFICATION BUS-20-073.
 - THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF
MEET THE EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 - FOR LEAD FREE PART NUMBERS, ADD AN "LF" SUFFIX.
EXAMPLE: 63346-XXYLF
 - ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260° FOR
60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR
PHASE REFLOW OVEN.

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
ltr	ecr no.	dr	date	linear	0.X ± 0.3	projection	COPY	title	product family	code	sheet
F					0.XX ± 0.13						
				angles	.XXX ± .051		MM	METAL POWER HEADER 1 MOD, 5 ROW STB	METAL	213	2
					0° ± 2°						
				dr	T.BRUNGARD 11/19/99	scale 2:1	A	63346	size A	cage code 22526	4
				enrg	M.STRAWSE 11/19/99						
				chr	M.STRAWSE 11/19/99						
				appd	M.STRAWSE 02/29/00						
sheet index	revision sheet										



METRAL P/N			CONTACT CODE MOD. I		METRAL P/N			CONTACT CODE MOD. I		METRAL P/N			CONTACT CODE MOD. I		METRAL P/N			CONTACT CODE MOD. I		
ROW			I 2		ROW			I 2		ROW			I 2		ROW			I 2		
63346-X01 SEE NOTE 9 LEAD FREE OPTION			E		P04 P04		63346-X05 SEE NOTE 9 LEAD FREE OPTION			E		P05 P05		63346-X09 SEE NOTE 9 LEAD FREE OPTION			E		P02 P02	
			D		P04 P04					D		P05 P05					D		P02 P02	
			C		P04 P04					C		P05 P05					C		P02 P02	
			B		P04 P04					B		P02 P02					B		P02 P02	
			A		P04 P04					A		P05 P05					A		P02 P02	
METRAL P/N			CONTACT CODE MOD. I		METRAL P/N			CONTACT CODE MOD. I		METRAL P/N			CONTACT CODE MOD. I		METRAL P/N			CONTACT CODE MOD. I		
ROW			I 2		ROW			I 2		ROW			I 2		ROW			I 2		
63346-X02 SEE NOTE 9 LEAD FREE OPTION			E		P04 P04		63346-X06 SEE NOTE 9 LEAD FREE OPTION			E		P01 P01		63346-X10 SEE NOTE 9 LEAD FREE OPTION			E		P03 P03	
			D		P04 P04					D		P01 P01					D		P03 P03	
			C		P04 P04					C		P02 P02					C		P03 P03	
			B		P04 P04					B		P03 P03					B		P03 P03	
			A		P01 P01					A		P03 P03					A		P03 P03	
METRAL P/N			CONTACT CODE MOD. I		METRAL P/N			CONTACT CODE MOD. I		METRAL P/N			CONTACT CODE MOD. I		METRAL P/N			CONTACT CODE MOD. I		
ROW			I 2		ROW			I 2		ROW			I 2		ROW			I 2		
63346-X03 SEE NOTE 9 LEAD FREE OPTION			E		P05 P05		63346-X07 SEE NOTE 9 LEAD FREE OPTION			E		P01 P01								
			D		P01 P01					D		P01 P01								
			C		P05 P05					C		P01 P01								
			B		P05 P05					B		P03 P03								
			A		P01 P01					A		P01 P01								
METRAL P/N			CONTACT CODE MOD. I		METRAL P/N			CONTACT CODE MOD. I		METRAL P/N			CONTACT CODE MOD. I		METRAL P/N			CONTACT CODE MOD. I		
ROW			I 2		ROW			I 2		ROW			I 2		ROW			I 2		
63346-X04 SEE NOTE 9 LEAD FREE OPTION			E		P01 P01		63346-X08 SEE NOTE 9 LEAD FREE OPTION			E		P05 P05								
			D		P01 P01					D		P05 P05								
			C		P01 P01					C		P05 P05								
			B		P01 P01					B		P05 P05								
			A		P01 P01					A		P05 P05								

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCj www.fcconnect.com															
ltr		ecn no.		dr		date		linear		0. X ±0.3		COPY		title METRAL POWER HEADER I MOD, 5 ROW STB											
F								0. XX ±0.13		projection															
								.XXX ±.051		0° ±2°		MM													
								angles		0° ±2°		scale													
								dr		T.BRUNGARD 11/19/99		product family		METRAL											
								enrg		M.STRAWSER 11/19/99		size		dwg no		213									
								chr		M.STRAWSER 11/19/99		A		63346		sheet									
								appd		M.STRAWSER 02/29/00		2:1				3									
sheet		index		revision		sheet																			