

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0533750310](#)
Status: **Active**
Overview: [Mini-Lock™ Wire-to-Board Connector System](#)
Description: 2.50mm Pitch Mini-Lock™ Wire-to-Board Header, Vertical, Friction and Positive Lock, 3 Circuits

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-51103-005-001 \(PDF\)](#)
[Product Specification PS-51163-002-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General


Product Family PCB Headers
Series [53375](#)
Application Signal, Wire-to-Board
MolexKits Yes
Overview [Mini-Lock™ Wire-to-Board Connector System](#)
Product Name Mini-Lock™
UPC 800753563612

Physical

Breakaway No
Circuits (Loaded) 3
Circuits (maximum) 3
Color - Resin Natural
Durability (mating cycles max) 30
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Polyester
Net Weight 469.000/mg
Number of Rows 1
Orientation Vertical
PC Tail Length 3.40mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Bag
Pitch - Mating Interface 2.50mm
Polarized to PCB Yes
Shrouded Fully
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40°C to +105°C
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 3.0A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series

[53375 Series](#)

Mates With

Mini-Lock™ Wire-to-Board and Wire-to-Wire
Crimp Terminal [51103](#) , [51102](#) , [51163](#)

Voltage - Maximum	250V
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-51103-005-001, PS-51163-002-001
Sales Drawing	SD-53375-001

This document was generated on 09/01/2017
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION