








1. FOR MINI-APPLICATOR CRIMPING.
2. WIRE RANGE IS 22-26 AWG AND INSULATION RANGE IS 1.02/1.27 [.040/.050].
3. PLATED WITH 0.76µm [.000030] GOLD ON INSIDE OF LOCALIZED GOLD PLATE AREA, GOLD FLASH ON ZONE 1, ALL OVER 1.27µm [.000050] NICKEL UNDERPLATE.
-OR-
GOLD FLASH OVER PALLADIUM-NICKEL 0.76µm [.000030] TOTAL ON INSIDE OF LOCALIZED GOLD PLATE AREA, GOLD FLASH ON ZONE 1, ALL OVER 1.27µm [.000050] NICKEL UNDERPLATE.
4. GOLD FLASH PER MIL-G-45204 ON INSIDE OF LOCALIZED GOLD PLATE AREA, GOLD FLASH PER MIL-G-45204 ON ZONE 1, ALL OVER 0.76µm [.000030] NICKEL UNDERPLATE PER QQ-N-290.
5. 0.025µm [.000001] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 2.54 [.100] MIN., TIN PLATED WIRE BARRELS, ALL OVER 0.76µm [.000030] NICKEL PER QQ-N-290.
6. SELECTIVE GOLD PLATED 0.76µm [.000030] THICK PER MIL-G-45204 ON MATING END FOR A LENGTH OF 2.54 [.100] MIN., TIN PLATED WIRE BARRELS, ALL OVER 1.27µm [.000050] NICKEL PER QQ-N-290.
7. COLOR CODE YELLOW IN THIS AREA INDICATES 22-26 AWG WIRE RANGE. ONLY LOOSE PIECE PART NUMBERS ARE COLOR CODED.
8. GOLD PLATING MAY NOT APPEAR ON CARRIER STRIP.



SECTION X-X
INSULATION BARREL
SCALE 20:1



SECTION Y-Y
WIRE BARREL
SCALE 20:1

OBSOLETE	STANDARD	6	LOOSE PIECE	1-745253-6
OBSOLETE	STANDARD	6	STRIP	1-745253-4
OBSOLETE	STANDARD	5	LOOSE PIECE	1-745253-3
OBSOLETE	STANDARD	5	STRIP	1-745253-1
	STANDARD	4	LOOSE PIECE	745253-7
	STANDARD	3	LOOSE PIECE	745253-6
	STANDARD	4	STRIP	745253-3
	STANDARD	3	STRIP	745253-2
PACKAGING TYPE		FINISH	TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES

± -
± -
± 0.13 [.005]
± -
± -
± 2°

MATERIAL
PHOS. BRONZE PER

SEE TABLE

DWN
S. WELDON
CHK
J. GERACE
APVD
R. BAER

11-3-80
11-5-80
11-10-80

NAME
SOCKET CONTACT, SIZE 20 DF,
22-26 AWG, W/.040-.050
DIA INSULATION SUPPORT

SIZE
A1

CAGE CODE
00779

DRAWING NO
745253

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE 15:1

SHEET 1 OF 1

REV M

4805 (3/11)