










LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			R	REVISED PER ECO-12-012349	28MAR13	BL	AC



DETAIL G

RECOMMENDED P.C. BOARD DIMMENSIONS.



LEAD FREE

GENERAL TOLERANCE

10 ≥ : ±0.2
30 ≥ > 10: ±0.25
100 ≥ > 30: ±0.3
ANGLES: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.ISHIKAWA 13OCT88 CHK 19AUG2004 Steven Yao APVD 19AUG2004 JulYee Zhu PRODUCT SPEC 108-60038 APPLICATION SPEC WEIGHT		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME AMP CHAMP .050 CONNECTOR (B-T-B) RECEPTACLE CONECTOR (HORIZONTAL WITH RETENTION LEG)	
MATERIAL  		FINISH		SIZE A2 CAGE CODE 00779 DRAWING NO C-5175474 RESTRICTED TO	
CUSTOMER DRAWING				SCALE NTS SHEET 1 of 1 REV R	

OBSOLETE	6-	-2		130	64	81.28	86.82	88.68	92.48	83.18
	6-	-1		120	59	74.93	80.47	82.33	86.13	76.83
	6-	-0		100	49	62.23	67.77	69.63	73.43	64.13
	5-	-9		80	39	49.53	55.07	56.93	60.73	51.43
	5-	-8		68	33	41.91	47.45	49.31	53.11	43.81
	5-	-7		60	29	36.83	42.37	44.23	48.03	38.73
	5-	-6		50	24	30.48	36.02	37.88	41.68	32.38
	5-	-5		40	19	24.13	29.67	31.53	35.33	26.03
	5-	-3		30	14	17.78	23.32	25.18	28.98	19.68
	5-	-1	0.00076	20	9	11.43	16.97	18.83	22.63	13.33
	4-	-2		130	64	81.28	86.82	88.68	92.48	83.18
	4-	-1		120	59	74.93	80.47	82.33	86.13	76.83
	4-	-0		100	49	62.23	67.77	69.63	73.43	64.13
	3-	-9		80	39	49.53	55.07	56.93	60.73	51.43
	3-	-8		68	33	41.91	47.45	49.31	53.11	43.81
	3-	-7		60	29	36.83	42.37	44.23	48.03	38.73
	3-	-6		50	24	30.48	36.02	37.88	41.68	32.38
	3-	-5		40	19	24.13	29.67	31.53	35.33	26.03
	3-	-3		30	14	17.78	23.32	25.18	28.98	19.68
	3-	-1	0.0005	20	9	11.43	16.97	18.83	22.63	13.33
OBSOLETE	1-	-2		130	64	81.28	86.82	88.68	92.48	83.18
	1-	-1		120	59	74.93	80.47	82.33	86.13	76.83
	1-	-0		100	49	62.23	67.77	69.63	73.43	64.13
		-9		80	39	49.53	55.07	56.93	60.73	51.43
		-8		68	33	41.91	47.45	49.31	53.11	43.81
		-7		60	29	36.83	42.37	44.23	48.03	38.73
		-6		50	24	30.48	36.02	37.88	41.68	32.38
		-5		40	19	24.13	29.67	31.53	35.33	26.03
OBSOLETE		-4		36	17	21.59	27.13	28.99	32.79	23.49
		-3		30	14	17.78	23.32	25.18	28.98	19.68
	5175474-1		0.0002	20	9	11.43	16.97	18.83	22.63	13.33
	PART NO.	AU PLATE	POS.	n	A	B	C	D	E	