


# SOT23 SILICON PLANAR HIGH SPEED SWITCHING COMMON ANODE DIODE PAIR


FMMD2836

ISSUE 1 – FEBRUARY 1995

## DIODE PIN CONNECTION



PARTMARKING DETAIL – A2



SOT23

## ABSOLUTE MAXIMUM RATINGS.

| PARAMETER                                   | SYMBOL         | VALUE       | UNIT       |
|---------------------------------------------|----------------|-------------|------------|
| Breakdown Voltage ( $I_R=100\mu A$ )        | $V_{(BR)}$     | 75          | V          |
| Average Rectified Forward Current †         | $I_{F(AV)}$    | 100         | mA         |
| Repetitive Peak Forward Surge Current       | $I_{FRM}$      | 200         | mA         |
| Power Dissipation at $T_{amb} = 25^\circ C$ | $P_{tot}$      | 330         | mW         |
| Operating and Storage Temperature Range     | $T_j; T_{stg}$ | -55 to +150 | $^\circ C$ |

## ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^\circ C$ unless otherwise stated).


| PARAMETER         | SYMBOL   | MIN. | MAX.              | UNIT        | CONDITIONS.                             |
|-------------------|----------|------|-------------------|-------------|-----------------------------------------|
| Forward Voltage   | $V_F$    |      | 1.0<br>1.0<br>1.2 | V<br>V<br>V | $I_F=10mA$<br>$I_F=50mA$<br>$I_F=100mA$ |
| Reverse Current   | $I_R$    |      | 100               | nA          | $V_R=50V$                               |
| Recovery Time*    | $t_{rr}$ |      | 6                 | ns          | $I_F=I_R=10mA, I_{R(REC)}=1.0mA$        |
| Diode Capacitance | $C_d$    |      | 4                 | pF          | $V_R=0, f=1MHz$                         |

\*For switching test circuit diagram see page

†Over any 20ms period


Spice parameter data is available upon request for this device

# FMMD2836



| DIM | Millimeters |      | Inches    |        |
|-----|-------------|------|-----------|--------|
|     | Min         | Max  | Min       | Max    |
| A   | 2.67        | 3.05 | 0.105     | 0.120  |
| B   | 1.20        | 1.40 | 0.047     | 0.055  |
| C   | -           | 1.10 | -         | 0.043  |
| D   | 0.37        | 0.53 | 0.0145    | 0.021  |
| F   | 0.085       | 0.15 | 0.0033    | 0.0059 |
| G   | NOM 1.9     |      | NOM 0.075 |        |
| K   | 0.01        | 0.10 | 0.0004    | 0.004  |
| L   | 2.10        | 2.50 | 0.0825    | 0.0985 |
| N   | NOM 0.95    |      | NOM 0.37  |        |

## Package Details



Zetex plc.  
Fields New Road, Chadderton, Oldham, OL98NP, United Kingdom.  
Telephone: 0161627 5105 (Sales), 0161627 4963 (General Enquiries)  
Facsimile: 0161627 5467

Zetex GmbH  
Drosselweg 30  
D81827 München  
Germany  
Telefon: (089) 430 90 29  
Fax: (089) 439 37 64

Zetex Inc.  
87 Modular Avenue  
Commack NY11725  
U.S.A.  
Telephone: (516) 5437100  
Fax: (516) 8647630

Zetex (Asia) Ltd.  
3510 Metroplaza, Tower 2  
Hing Fong Road, Kwai Fong  
Hong Kong  
Telephone: 2610 0611  
Fax: 2425 0494

These are supported by  
agents and distributors in  
major countries worldwide  
©Zetex plc 1995

This publication is issued to provide outline information only which (unless agreed by the Company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contract or be regarded as a representation relating to the products or services concerned. The Company reserves the right to alter without notice the specification, design, price or conditions of supply of any product or service.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Diodes Incorporated:](#)

[FMMD2836TA](#) [FMMD2836TC](#)