


**Panasonic**  
ideas for life

## MINIATURE PC BOARD TYPE POWER RELAY

# JS RELAYS



mm inch

## FEATURES

- Miniature size with universal terminal footprint
- High contact capacity: 10 A
- Class B coil insulation type available
- TV-5 type available (Standard type)
  - 1 Form A type → TV-5
  - 1 Form C type → TV-5 (N.O. side only)
- VDE, TÜV also approved
- Sealed construction for automatic cleaning (Standard type)

## SPECIFICATIONS

### Contact

| Types                                                            |                                                                                                                    | Standard type                                  | High power type                                 |
|------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------|------------------------------------------------|-------------------------------------------------|
| Arrangement                                                      |                                                                                                                    | 1 Form A,<br>1 Form C                          | 1 Form A                                        |
| Initial contact resistance, max.<br>(By voltage drop 6 V DC 1 A) |                                                                                                                    | 100 mΩ                                         |                                                 |
| Contact material                                                 |                                                                                                                    | Silver alloy                                   |                                                 |
| Rating<br>(resistive<br>load)                                    | Nominal switching capacity                                                                                         | 10 A 250 V AC<br>10 A 125 V AC<br>6 A 277 V AC | 10 A 250 V AC<br>10 A 125 V AC<br>10 A 277 V AC |
|                                                                  | Max. switching power                                                                                               | 2,500 VA                                       |                                                 |
|                                                                  | Max. switching voltage                                                                                             | 250 V AC, 100 V DC                             |                                                 |
|                                                                  | Max. switching current                                                                                             | 10 A (AC), 5 A (DC)                            |                                                 |
|                                                                  | Min. switching capacity <sup>#1</sup>                                                                              | 100 mA, 5 V DC                                 |                                                 |
| Expected<br>life (min.<br>ope.)                                  | Mechanical<br>(at 180 cpm)                                                                                         | 10 <sup>7</sup>                                |                                                 |
|                                                                  | Electrical at 10 A<br>125 V AC,<br>6 A 277 V AC resistive<br>(standard)<br>10 A 277 V AC<br>resistive (High power) | 10 <sup>5</sup>                                | 2×10 <sup>5</sup>                               |
|                                                                  | 10 A 250 V AC<br>resistive<br>(Standard: at 20 cpm)<br>(High power: at 20<br>cpm, 105°C 221°F)**                   | 5 × 10 <sup>4</sup><br>(No contact<br>only)    | 1.5 × 10 <sup>5</sup>                           |
|                                                                  |                                                                                                                    |                                                |                                                 |

\*\* Holding voltage should be 60% V of nominal voltage

### Coil

|                         |        |
|-------------------------|--------|
| Nominal operating power | 360 mW |
|-------------------------|--------|

<sup>#1</sup> This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

### Remarks

\*<sup>1</sup> Detection current: 10mA

\*<sup>2</sup> Excluding contact bounce time

\*<sup>3</sup> Half-wave pulse of sine wave: 11ms; detection time: 10μs

### Characteristics

|                                                                                                                            |                             |                                                                                                                 |                                          |
|----------------------------------------------------------------------------------------------------------------------------|-----------------------------|-----------------------------------------------------------------------------------------------------------------|------------------------------------------|
| Max. operating speed                                                                                                       |                             | 20 cpm                                                                                                          |                                          |
| Types                                                                                                                      |                             | Standard type                                                                                                   | High power type                          |
| Initial insulation resistance                                                                                              |                             | Min. 100 MΩ (at 500 V DC)                                                                                       |                                          |
| Initial breakdown voltage* <sup>1</sup>                                                                                    | Between open contacts       | 750 Vrms for 1 min.                                                                                             |                                          |
|                                                                                                                            | Between contacts and coil   | 1,500 Vrms for 1 min.                                                                                           |                                          |
| Operate time* <sup>2</sup><br>(at nominal voltage)                                                                         |                             | Approx. 10 ms                                                                                                   |                                          |
| Release time(without diode)* <sup>2</sup> (at nominal voltage)                                                             |                             | Approx. 10 ms                                                                                                   |                                          |
| Temperature rise (at nominal voltage)                                                                                      |                             | Max. 35°C,<br>resistive, nominal voltage<br>applied to coil.<br>Contact carrying current:<br>10A, at 85°C 185°F |                                          |
| Shock resistance                                                                                                           | Functional* <sup>3</sup>    | Min. 98 m/s <sup>2</sup> {10 G}                                                                                 |                                          |
|                                                                                                                            | Destructive* <sup>4</sup>   | Min. 980 m/s <sup>2</sup> {100 G}                                                                               |                                          |
| Vibration resistance                                                                                                       | Functional* <sup>5</sup>    | Approx. 98 m/s <sup>2</sup> {10 G},<br>10 to 55 Hz at double<br>amplitude of 1.6 mm                             |                                          |
|                                                                                                                            | Destructive                 | Approx. 117.6 m/s <sup>2</sup> {12 G},<br>10 to 55 Hz at double<br>amplitude of 2 mm                            |                                          |
| Conditions for operation,<br>transport and storage* <sup>6</sup><br>(Not freezing and<br>condensing at low<br>temperature) | Ambient temp.* <sup>7</sup> | -40°C to<br>+85°C<br>-40°F to<br>+185°F                                                                         | -40°C to<br>+105°C<br>-40°F to<br>+221°F |
|                                                                                                                            | Humidity                    | 5 to 85% R.H.                                                                                                   |                                          |
| Unit weight                                                                                                                |                             | Approx. 12 g .423 oz                                                                                            |                                          |

\*<sup>4</sup> Half-wave pulse of sine wave: 6ms

\*<sup>5</sup> Detection time: 10μs

\*<sup>6</sup> Refer to 6. Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT

\*<sup>7</sup> When using relays in a high ambient temperature, consider the pick-up voltage rise due to the high temperature (a rise of approx. 0.4% V for each 1°C 33.8°F with 20°C 68°F as a reference) and use a coil impressed voltage that is within the maximum allowable voltage range.

## TYPICAL APPLICATIONS

- Home appliances  
Air conditioner, heater, etc.
- Automotive  
Power-window, car antenna, door-lock, etc.
- Office machines  
PPC, facsimile, etc.
- Vending machines

ORDERING INFORMATION



| Contact arrangement                                                             | Protective construction                    | Coil insulation class                            | Coil voltage (DC)            | Environmental support                                                                                               |
|---------------------------------------------------------------------------------|--------------------------------------------|--------------------------------------------------|------------------------------|---------------------------------------------------------------------------------------------------------------------|
| 1: 1 Form C (Standard)<br>1a: 1 Form A (Standard)<br>1aP: 1 Form A (High Power) | Nil: Sealed type<br>F: Flux-resistant type | Nil: Class E insulation<br>B: Class B insulation | 5, 6, 9, 12, 18,<br>24, 48 V | F: RoHS Directive conforming type (AgSnO <sub>2</sub> type)<br>Nil: RoHS Directive non-conforming type (AgCdO type) |


UL/CSA, VDE, TÜV (Standard type only) approved type is standard.  
Notes: 1. Standard packing: Carton: 100 pcs. Case: 500 pcs.  
2. When ordering TV rated (TV-5) types, add suffix -TV.  
3. Contact arrangement 1aP type is Flux-resistant type only (class B or class F insulation).  
Please consult us for coil insulation class F.

COIL DATA

| Part No.      |              |                     |               |                        | Nominal<br>voltage,<br>V DC | Pick-up<br>voltage,<br>V DC (max.)<br>(at 20°C<br>68°F) | Drop-out<br>voltage,<br>V DC (min.)<br>(at 20°C<br>68°F) | Coil<br>resistance,<br>Ω (±10%)<br>(at 20°C<br>68°F) | Nominal<br>operating<br>current,<br>mA (±10%)<br>(at 20°C<br>68°F) | Nominal<br>operating<br>power, mW<br>(at 20°C<br>68°F) | Max.<br>allowable<br>voltage<br>(at 85°C<br>185°F) |
|---------------|--------------|---------------------|---------------|------------------------|-----------------------------|---------------------------------------------------------|----------------------------------------------------------|------------------------------------------------------|--------------------------------------------------------------------|--------------------------------------------------------|----------------------------------------------------|
| Standard type |              |                     |               | High Power type        |                             |                                                         |                                                          |                                                      |                                                                    |                                                        |                                                    |
| Sealed type   |              | Flux-resistant type |               | Flux-resistant<br>type |                             |                                                         |                                                          |                                                      |                                                                    |                                                        |                                                    |
| 1 Form A      | 1 Form C     | 1 Form A            | 1 Form C      | 1 Form A               |                             |                                                         |                                                          |                                                      |                                                                    |                                                        |                                                    |
| JS1a-5V (-F)  | JS1-5V (-F)  | JS1aF-5V (-F)       | JS1F-5V (-F)  | JS1aPF-B-5V (-F)       | 5                           | 3.5                                                     | 0.5                                                      | 69.4                                                 | 72                                                                 | 360                                                    | 130%V<br>of<br>nominal<br>voltage                  |
| JS1a-6V (-F)  | JS1-6V (-F)  | JS1aF-6V (-F)       | JS1F-6V (-F)  | JS1aPF-B-6V (-F)       | 6                           | 4.2                                                     | 0.6                                                      | 100                                                  | 60                                                                 |                                                        |                                                    |
| JS1a-9V (-F)  | JS1-9V (-F)  | JS1aF-9V (-F)       | JS1F-9V (-F)  | JS1aPF-B-9V (-F)       | 9                           | 6.3                                                     | 0.9                                                      | 225                                                  | 40                                                                 |                                                        |                                                    |
| JS1a-12V (-F) | JS1-12V (-F) | JS1aF-12V (-F)      | JS1F-12V (-F) | JS1aPF-B-12V (-F)      | 12                          | 8.4                                                     | 1.2                                                      | 400                                                  | 30                                                                 |                                                        |                                                    |
| JS1a-18V (-F) | JS1-18V (-F) | JS1aF-18V (-F)      | JS1F-18V (-F) | JS1aPF-B-18V (-F)      | 18                          | 12.6                                                    | 1.8                                                      | 900                                                  | 20                                                                 |                                                        |                                                    |
| JS1a-24V (-F) | JS1-24V (-F) | JS1aF-24V (-F)      | JS1F-24V (-F) | JS1aPF-B-24V (-F)      | 24                          | 16.8                                                    | 2.4                                                      | 1,600                                                | 15                                                                 |                                                        |                                                    |
| JS1a-48V (-F) | JS1-48V (-F) | JS1aF-48V (-F)      | JS1F-48V (-F) | JS1aPF-B-48V (-F)      | 48                          | 33.6                                                    | 4.8                                                      | 6,400                                                | 7.5                                                                |                                                        |                                                    |


DIMENSIONS

mm inch




Note: Terminal No. 4 is only for Standard  
1 Form C type  
General tolerance: ±0.3 ±0.12

Schematic (Bottom view)




PC board pattern (Bottom view)



Tolerance: ±0.1 ±0.004


## REFERENCE DATA

### 1. Maximum value for switching capacity




### 2. Operate/release time

Sample: 25 pcs., JS1-12V




### 3. Life curve

Ambient temperature: Room temperature




### 4-(1). Coil temperature rise

Sample: 5 pcs., JS1a-24V  
Measured portion: Inside the coil  
Contact current: 5 A




### 4-(2). Coil temperature rise

Sample: 5 pcs., JS1a-24V  
Measured portion: Inside the coil  
Contact current: 10 A



### 5. Ambient temperature characteristics

Sample: 6 pcs., JS1-12V




### 6. Electrical life test


(10 A 125 V AC, resistive load)

Sample: 6 pcs., JS1-12V  
Operating speed: 20 cpm  
Ambient temperature: room temperature


(Circuit)



### Change of pick-up and drop-out voltage



### Change of contact resistance



**For Cautions for Use, see Relay Technical Information**