




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
CM	53					
		AB6	REVISED	PER ECR-17-006277	24MAY2017	BW

D


C

B



A




- MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™CAP OR HEADER.
 - SMALL NICKS ARE PERMITTED ON THE CIRCUIT TOWERS WHICH COULD INCREASE THE INITIAL HOUSING MATING FORCE BY UP TO 4.4 NEWTONS [1.0 LBS]. NO INDIVIDUAL NICKED TOWER SHALL INCREASE THIS FORCE BY OVER 2.2 NEWTONS [.5 LBS].
 - DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
- △4 FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION,OPTIONAL.
- △5 NOT MANUFACTURED IN U.S.
- △6 UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
- △7 MATERIAL CORRESPONDING TO THE REQUIREMENT OF IEC60335-1 (INCL. GWT 750°C WITHOUT FLAME)




VIEW A—A
350779-4 ONLY




DETAIL A
OPTIONAL CONSTRUCTION



DETAIL B
350779-4 ONLY



350779-4 3-DIMENSIONAL MODEL
NTS



3-DIMENSIONAL MODEL
NTS

△ NATURAL	350779-5
BLACK	1-350779-9
GRAY	1-350779-8
BLUE	1-350779-6
GREEN	1-350779-5
YELLOW	1-350779-4
ORANGE	1-350779-3
RED	1-350779-2
BROWN	1-350779-1
△	350779-4
NATURAL	350779-1
COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL	03FEB95	TE Connectivity	
		CHK R. SWING	03FEB95		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPROD D SELF	03FEB95	NAME	PLUG, 4 CIRCUIT, UNIVERSAL MATE-N-LOK™
	0 PLC ± -	PRODUCT SPEC		SIZE	—
	1 PLC ± 0.4	APPLICATION SPEC		CAGE CODE	—
	2 PLC ± 0.20			DRAWING NO	—
	3 PLC ± -			RESTRICTED TO	—
MATERIAL NYLON,UL 94V-0	4 PLC ± -	WEIGHT		SIZE	—
	ANGLES FINISH			SCALE	—
		CUSTOMER DRAWING		1 OF 1	REV AB6