




| DASH<br>NUMBER | MODEL<br>NUMBER | IMPD<br>OHMS |
|----------------|-----------------|--------------|
| -1             | BJ224           | 50           |
| -2             | UBJ224          | 75           |

DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO EMERSON CONNECTIVITY SOLUTIONS AND SHALL NOT  
BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR  
MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION


# REVISIONS

| REV | DESCRIPTIONS          | DATE    | APPROVED |
|-----|-----------------------|---------|----------|
| B   | REVISED PER ECO 16588 | 9/22/09 | Lm       |

RED INDICATES ORIGINAL



SCALE 2/1



RECOMMENDED  
PANEL CUTOUT  
SCALE 3/1

3. SOCKET CONTACT COAXIAL BNC TYPE  
NON-INSULATED FEED THRU BULKHEAD  
JACK, 50 AND 75  $\Omega$  VERSIONS

2. MAXIMUM PANEL THICKNESS: .156

1. FINISH: TFS-1A, (NICKEL)

NOTES: UNLESS OTHERWISE SPECIFIED.

|                                                                                                                                     |         |                                                                  |  |                                                                                                                                              |                           |                                                                                                 |             |
|-------------------------------------------------------------------------------------------------------------------------------------|---------|------------------------------------------------------------------|--|----------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|-------------------------------------------------------------------------------------------------|-------------|
| INTERPRET DRAWING PER<br>MIL-STD-100.<br>DIMENSIONS ARE IN INCHES<br>AND INCLUDE FINISH<br>THICKNESS<br>UNLESS OTHERWISE SPECIFIED. |         | TOL: UNLESS SPECIFIED.<br>.XX ± .02<br>.XXX ± .010<br>ANGLE ± 1° |  |  <b>cinch</b><br>CONNECTIVITY SOLUTIONS<br>a bell group |                           | Cinch Connectivity Solutions<br>299 Johnson Ave. Ste. 100<br>Waseca, MN 56093<br>1-800-247-8256 |             |
| DRN<br>M JOHNSON                                                                                                                    | 9-16-09 | MATERIAL:                                                        |  | TITLE:<br><br>BJ224/UBJ224                                                                                                                   |                           |                                                                                                 |             |
| CHK<br><i>Lm</i>                                                                                                                    | 9/16/09 | FINISH:                                                          |  |                                                                                                                                              |                           |                                                                                                 |             |
| QUALITY                                                                                                                             |         |                                                                  |  |                                                                                                                                              |                           |                                                                                                 |             |
| MANUF                                                                                                                               |         |                                                                  |  |                                                                                                                                              |                           |                                                                                                 |             |
| APPROVED<br><i>Lm</i>                                                                                                               | 9/16/09 |                                                                  |  | SIZE<br><b>A</b>                                                                                                                             | CAGE CODE<br><b>14949</b> | DRAWING NO.<br>1-0590                                                                           | REV.<br>B   |
| PROVE FILE NO.<br>1-0590                                                                                                            |         | DO NOT SCALE DWG                                                 |  | SCALE<br>3/1                                                                                                                                 | DATE<br>10-11-00          |                                                                                                 | SHEET<br>IC |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Cinch Connectivity Solutions:

[6-0001-1](#) [AD1W](#) [AD1WHD](#) [ADMW12](#) [ADRMF70](#) [BJ150](#) [BJ157](#) [BJ158](#) [BJ21](#) [BJ28](#) [BJ376](#) [BJ72](#) [BJ73](#) [BJ75](#)  
[BJ77FL](#) [BJ77TL](#) [BJ78](#) [BJ78HS](#) [BN73](#) [CBBJ379](#) [CBBJR26](#) [CBBJR79](#) [CBBJR79TL](#) [CBJ157](#) [CBJ70](#) [J158](#) [J3W](#)  
[J72](#) [LPTW-78](#) [PL155AC-201](#) [PL3455ACS-201](#) [PL75-47](#) [PL75C-201](#) [RT1L](#) [RT1S](#) [RT4S](#) [UAD258](#) [UADRMF220](#)  
[UBJ228](#) [UBJ28](#) [UCBJE20-1](#) [UCBJR220](#) [UCBBJR250-G](#) [UCBJ20F](#) [700-0024](#) [AD158FL](#) [AD378](#) [AD78FL](#) [AD78TL](#)  
[ADI95](#) [ADM2](#) [ADRMF370](#) [BJ120](#) [BJ152FL](#) [BJ153](#) [BJ157HS](#) [BJ158FL](#) [BJ224](#) [BJ228](#) [BJ24](#) [BJ31](#) [BJ3150HS](#)  
[BJ3157](#) [BJ3158](#) [BJ3450P](#) [BJ376HS](#) [BJ378HS](#) [BJ38](#) [BJ380](#) [BJ450FLS](#) [BJ450PS](#) [BJ450RS](#) [BJ450WS](#) [BJ47](#)  
[BJ72TL](#) [BJ75TL](#) [BJ77HS](#) [BJ78TL](#) [BJ98-2](#) [BN153FL](#) [BN373](#) [BN73TL](#) [BN83-1](#) [C24T3A](#) [C24T3B](#) [C24T3C](#)  
[C24T3D](#) [C24T3U](#) [CBBJR39A](#) [CBBJR79FL](#) [CBJ157FL](#) [CBJ20](#) [CBJ70FL](#) [CBJR3157](#) [HDVDPMN](#) [HDVDPN](#) [J11D](#)  
[J152](#) [J24WMSTHF-75](#) [J3](#)