


Home: Application Tooling >

Part Number: 11-02-0004

Hand Insertion Tool



Series image - Reference only

Status: **OBSOLETE**

Replacement: [63812-0000](#)

Series: [2813](#)

Category: Application Tooling

Engineering/Old PN: HT2813

Go to **Part Detail**

CHECK DISTRIBUTOR INVENTORY

[Add to My Parts](#)

[Email this page](#)

Product Environmental Compliance

[EU ELV](#):Product not active

[EU RoHS](#):Product not active

[EU RoHS Phthalates](#):Product not active

[China RoHS](#):

[REACH SVHC](#):Product not active

[Low-Halogen Status](#):Product not active

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements

EU RoHS, REACH SVHC, & Low-Halogen

Multiple Part Industry Compliance Documents

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Questions on Product Environmental Compliance? EmailProductCompliance@molex.com

Request Molex's CMRT from conflictminerals@molex.com

Part Detail

COLLAPSE ALL

General

Status	Obsolete
Category	Application Tooling
Series	2813
Function	Insertion
Geographic Area	Japan
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Product Name	N/A
Tool Type	Handtool
UPC	800753609457
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number	HT2813
--------------------	--------

Reference - Drawing Numbers

Application Tooling Documents	ATS-011020004, HT-2813, TM-638000029, TM-638000029CN, TM-638000029DE, TM-638000029FR, TM-638000029IT, TM-638000029JP, TM-638000029KR, TM-638000029MY, TM-638000029PL, TM-638000029RU, TM-638000029SK, TM-638000029SP, TM-638000029TH, TM-638000029TW, TM-638000029VN
-------------------------------	--

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Description	Product #
KK® 254 Crimp Terminal, 22-30 AWG, Bag, Hot Tin (Sn) Dip Plating	08-50-0114
KK® Cat Ear Crimp Terminal 5159, 22-28 AWG, Reel, Phosphor Bronze, Tin (Sn) Plating	08-70-0048
KK® Cat Ear Crimp Terminal 5159, 22-28 AWG, Bag, Phosphor Bronze, Tin (Sn) Plating	08-70-0049
KK® Cat Ear Crimp Terminal 5159, 22-28 AWG, Reel, Brass, Tin (Sn) over Copper Plating	08-70-0064
KK® Cat Ear Crimp Terminal 5159, 22-28 AWG, Bag, Brass, Tin (Sn) over Copper Plating	08-70-0069
KK® 254 Crimp Terminal, 22-28 AWG, 0.35µm Gold (Au), Nickel (Ni) Under-Plate, Phosphor Bronze, Loose	39-00-0381

PRODUCTS

Antennas

Application Tooling

Cable Assemblies

Connected Lighting

Connectors

Copper Flex

Electrical Products

Industrial Automation

Membrane Switches

Optical Solutions

Printed Electronic Solutions

QUICK LINKS

Company Information

Contact Molex

Cross-Reference

Koch Industries

Industries

Investor Relations

Literature

Molex Racing

Press Room / Press Releases

Product Index

Sitemap

Terms & Conditions

RESOURCES

Supply Chain Transparency

Business Continuity

Compliance

ecocare

Feedback | Help

Jobs

Legal | Trademarks

Mobile Site

Supplier Portal

Privacy Policy

Tradeshows

STAY CONNECTED

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2017