




Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTE:
1. SUPPLIED WITH SILVER PLATED
HEX NUT AND INTERNAL TOOTH
LOCKWASHER.

CAP. VALUE	1500pF
CAP. TOL.	+80% -20%
TEMP. COEF.	X5U
VOLT. RATING	500 VDC +85°C
OPERATING TEMP. RANGE	-55 TO +85°C
TESTED TO TUSONIX EQUIVALENT TO MIL-C-39014 FOR GROUP A INSPECTION INCLUDING SUMMARY TEST DATA	

MIL-C-39014/16 (CKR 75) PART NO.
M39014/16-0089

TUSONIX HI-RELIABILITY COMMERCIAL
REPLACEMENT PART NO.
2499-726-X5U0-152Z

X-2015 Rev-0	REVISION RECORD	Original Release C.O. 19980714-6-01 ADDED METRIC. S.M. 01-08-03 20030107-6-01	1		--TOLERANCES-- Unless Otherwise Specified	Title HI-RELIABILITY COMMERCIAL REPLACEMENT FOR M39014/16 (CKR75) FEED-THRU CAPACITOR	
					DECIMAL ± .031 [0.79]		
					ANGLES ±	Drawn S.M. 07-14-98	Scale 4 X
					TUSONIX TUCSON, ARIZONA	Approved T.C. 07-14-98	
						A	2499-726-X5U0-152Z