






NOTES

- 1 - ENCLOSURE FINISHED WITH GREEN EPOXY BASED ENAMEL COLOR NO. 34151 PER FEDERAL STANDARD 595
- 2 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
- 3 - CIRCUIT DIAGRAM, CATALOG LISTING AND DATE CODE ARE SHOWN ON NAMEPLATE
- 4 - SWITCH SEALED PER MIL-S-8805 SYMBOL 3
- 5 - EXTERNAL PLUNGER THROUGH HARDENED 43 ROCKWELL C MIN
- 6 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL
OPERATING FORCE ————	10-16 LB	CONTACT ARRANGEMENT		DO NOT SCALE PRINT
FULL OVERTRAVEL FORCE ————	30 LB MAX	SPNO (I) SPNC (I)		UNLESS OTHERWISE NOTED
RELEASE FORCE ————	8 LB MIN	28 VDC		DIMENSIONS ARE IN INCHES
PRETRAVEL ————	.040 MAX	LOAD	SEA LEVEL	TOLERANCES ARE:
DIFFERENTIAL TRAVEL ————	.020 MAX		50,000 FT.	ONE PLACE (.0) ±.030
OVERTRAVEL ————	.100 MIN			TWO PLACE (.00) ±.015
				THREE PLACE (.000) ±.005
		RES	4	ANGLES
		IND	2	
		MOTOR	4	
				WEIGHT 6.5 OZ MAX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1CH31-1B](#)