



TDK Corporation of America

[Close Window](#)

Inductors (Coils) Inductor Coils Part Number : MLG1608B18NJT000 Product Name : Multilayer Inductor for Ultra High Frequency Range TDK Series Name : MLG Series Application : No Data Available. Function : No Data Available. Description : No Data Available. Submit Sample Request Check Distributor Inventory Print Page Download Adobe PDF Viewer	MLG1608 TYPE APPEARANCE PHOTOGRAPH  < Prev No PDF Available Next >																																																														
Additional Search Tools: Application Catalog SEAT CCV TVCL Tech Notes																																																															
<table border="1"> <thead> <tr> <th>Property Name</th> <th>Property Description</th> </tr> </thead> <tbody> <tr> <td>Product Lifecycle Stage</td> <td>Production</td> </tr> <tr> <td>Part Number Replacement</td> <td><i>No Data Available.</i></td> </tr> <tr> <td>Lead (Pb) Free</td> <td>Yes</td> </tr> <tr> <td>Surface Mount</td> <td>Yes</td> </tr> <tr> <td>Construction Type</td> <td>multilayer type</td> </tr> <tr> <td>Mounting</td> <td>SMD</td> </tr> <tr> <td>Body Length (L)</td> <td>Nom 1.6 mm</td> </tr> <tr> <td>Body Width (W)</td> <td>Nom 0.8 mm</td> </tr> <tr> <td>Body Height (T)</td> <td>Max <i>No Data Available.</i></td> </tr> <tr> <td>Inductance</td> <td>Nom 0.018 μH</td> </tr> <tr> <td>Inductance Tolerance (%)</td> <td>Min -5 % Max 5 %</td> </tr> <tr> <td>Frequency of Inductance</td> <td>Nom 100 MHz</td> </tr> <tr> <td>Q</td> <td>Min 12</td> </tr> <tr> <td>Frequency of Q</td> <td>Nom 100 MHz</td> </tr> <tr> <td>Self Resonant Frequency</td> <td>Min 2.6 GHz</td> </tr> <tr> <td>D.C. Resistance</td> <td>Nom 0.16 Ohm</td> </tr> <tr> <td>D.C. Resistance</td> <td>Max 0.32 Ohm</td> </tr> <tr> <td>Rated Current</td> <td>Max 0.6 A</td> </tr> <tr> <td>Terminal Material</td> <td>Ag(100%)/Sn plating</td> </tr> <tr> <td>Polarity Marking</td> <td>Yes</td> </tr> <tr> <td>Magnetic Shielding</td> <td>No</td> </tr> <tr> <td>Soldering Method</td> <td>Reflow, Iron Soldering</td> </tr> <tr> <td>Measuring Equipment(Q)</td> <td>HP4291A+16193A, or equivalent</td> </tr> <tr> <td>Category Temperature Range</td> <td>Min -55 Cel Max 125 Cel</td> </tr> <tr> <td>Storage Temperature Range</td> <td>Min -55 Cel Max 125 Cel</td> </tr> <tr> <td>Country of Origin</td> <td>JPN</td> </tr> <tr> <td>Packing</td> <td>Punched (Paper)Taping [180mm Reel]</td> </tr> <tr> <td>Minimum Package Qty</td> <td>Nom 4000 Pcs</td> </tr> <tr> <td>Minimum Order Qty</td> <td>Nom 4000 Pcs</td> </tr> <tr> <td>Weight</td> <td>Nom 0.004 g</td> </tr> </tbody> </table>		Property Name	Property Description	Product Lifecycle Stage	Production	Part Number Replacement	<i>No Data Available.</i>	Lead (Pb) Free	Yes	Surface Mount	Yes	Construction Type	multilayer type	Mounting	SMD	Body Length (L)	Nom 1.6 mm	Body Width (W)	Nom 0.8 mm	Body Height (T)	Max <i>No Data Available.</i>	Inductance	Nom 0.018 μ H	Inductance Tolerance (%)	Min -5 % Max 5 %	Frequency of Inductance	Nom 100 MHz	Q	Min 12	Frequency of Q	Nom 100 MHz	Self Resonant Frequency	Min 2.6 GHz	D.C. Resistance	Nom 0.16 Ohm	D.C. Resistance	Max 0.32 Ohm	Rated Current	Max 0.6 A	Terminal Material	Ag(100%)/Sn plating	Polarity Marking	Yes	Magnetic Shielding	No	Soldering Method	Reflow, Iron Soldering	Measuring Equipment(Q)	HP4291A+16193A, or equivalent	Category Temperature Range	Min -55 Cel Max 125 Cel	Storage Temperature Range	Min -55 Cel Max 125 Cel	Country of Origin	JPN	Packing	Punched (Paper)Taping [180mm Reel]	Minimum Package Qty	Nom 4000 Pcs	Minimum Order Qty	Nom 4000 Pcs	Weight	Nom 0.004 g
Property Name	Property Description																																																														
Product Lifecycle Stage	Production																																																														
Part Number Replacement	<i>No Data Available.</i>																																																														
Lead (Pb) Free	Yes																																																														
Surface Mount	Yes																																																														
Construction Type	multilayer type																																																														
Mounting	SMD																																																														
Body Length (L)	Nom 1.6 mm																																																														
Body Width (W)	Nom 0.8 mm																																																														
Body Height (T)	Max <i>No Data Available.</i>																																																														
Inductance	Nom 0.018 μ H																																																														
Inductance Tolerance (%)	Min -5 % Max 5 %																																																														
Frequency of Inductance	Nom 100 MHz																																																														
Q	Min 12																																																														
Frequency of Q	Nom 100 MHz																																																														
Self Resonant Frequency	Min 2.6 GHz																																																														
D.C. Resistance	Nom 0.16 Ohm																																																														
D.C. Resistance	Max 0.32 Ohm																																																														
Rated Current	Max 0.6 A																																																														
Terminal Material	Ag(100%)/Sn plating																																																														
Polarity Marking	Yes																																																														
Magnetic Shielding	No																																																														
Soldering Method	Reflow, Iron Soldering																																																														
Measuring Equipment(Q)	HP4291A+16193A, or equivalent																																																														
Category Temperature Range	Min -55 Cel Max 125 Cel																																																														
Storage Temperature Range	Min -55 Cel Max 125 Cel																																																														
Country of Origin	JPN																																																														
Packing	Punched (Paper)Taping [180mm Reel]																																																														
Minimum Package Qty	Nom 4000 Pcs																																																														
Minimum Order Qty	Nom 4000 Pcs																																																														
Weight	Nom 0.004 g																																																														
Disclaimer: This information is to be used for reference purposes only and is subject to change by TDK without notice. It reflects an overview of the product characteristics/performance for the particular part number. For product specification information, please refer to TDK's general product specification. Please note that this standard part is not designed or warranted to meet any specifications of any																																																															

intermediate or end user different from or in addition to the specifications set forth in TDK's general product specification. Note also that this standard part has not been specially designed or manufactured for, nor is it intended or warranted for use in, or permitted to be resold for, specialized applications such as aviation, medical, and/or governmental/military applications (collectively, "Excluded Applications").

© TDK U.S.A. Corporation 2011. » [Privacy Statement](#) » [Careers](#) » [Site Map](#)
TDK Logo is a trademark or registered trademark of TDK Corporation.