

Customer Information Sheet

DRAWING No.: M80-850XXXX

SHEET 2 OF 2

IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

SPECIFICATIONS:

MATERIAL:

MOULDING = POLYAMIDE 46 UL94V-0, BLACK

CONTACTS = BERYLLIUM COPPER

FINISH:

CONTACTS (ALL OVER NICKEL):

01 = 0.3 μ GOLD CLIP, 3.5 μ 90/10 TIN/LEAD SHELL

45 = 0.30 μ GOLD CLIP, 0.28 μ GOLD SHELL

42 = 0.30 μ GOLD CLIP, 4.0 μ 100% TIN SHELL

ELECTRICAL:

CURRENT RATING (25°C) = 3.0A MAX.

CURRENT RATING (85°C) = 2.2A MAX.

WORKING VOLTAGE = 800V AC/DC

VOLTAGE PROOF = 1200V AC/DC

CONTACT RESISTANCE:

INITIAL = 20 m Ω MAX.

AFTER CONDITIONING = 25 m Ω MAX.

INSULATION RESISTANCE:

INITIAL = 1000 M Ω MIN.

AFTER CONDITIONING = 100 M Ω MIN.

MECHANICAL:

DURABILITY = 500 OPERATIONS

INSERTION FORCE ($\varnothing$ 0.5mm GAUGE) = 2N MAX

WITHDRAWAL FORCE ($\varnothing$ 0.5mm GAUGE) = 0.2N MIN





ENVIRONMENTAL:

TEMPERATURE RANGE = -55°C TO +125°C

PACKING:

TUBE

FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION C005XX (LATEST ISSUE)



SECTION X-X

ORDER CODE:

M80-850XXXX

TOTAL No. OF WAYS

04, 06, 08, 10, 12, 14, 16,
18, 20, 26, 34, 44

FINISH:

01 = TIN/LEAD SHELL, GOLD CLIP

45 = GOLD SHELL, GOLD CLIP

42 = 100% TIN SHELL, GOLD CLIP

MSP	II	27.05.15	12793
NAME	ISS.	DATE	C/NOTE
APPROVED:		M.PERREN	
CHECKED:		M.PLESTED	
DRAWN:		I. SANDY	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES

X. = $\pm$ 1mm

X.X = $\pm$ 0.50mm

X.XX = $\pm$ 0.10mm

X.XXX = $\pm$ 0.01mm

ANGLES = $\pm$ 5°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA:

mm²

TITLE:

DATAMATE DIL
VERTICAL PC TAIL SOCKET
ASSEMBLY (RoHS)

DRAWING NUMBER:

M80-850XXXX

SHT
2
OF
2