



Heat Shrinkable Tubing 6:1, adhesive lined in 1 m cuts

• **HA67**

Insulates, seals and protects large size differences between connectors and cables.

Features and Benefits


- High shrink ratio, heavy-duty heat shrinkable tubing
- Thermoplastic adhesive-lined tubing
- Conforms well to highly variable substrate dimensions
- Simplifies cable repair
- Passes over large connectors and shrinks onto much smaller cable jackets
- Environmental sealing and excellent insulation
- Resistant to impact and abrasion



One Step to the Web!



Heat Shrinkable Tubing 6:1 with adhesive



Due to the high shrink ratio HA67 is suitable for complex shapes and dimensions.

MATERIAL	Polyolefin, cross-linked (PO-X)
Shrink Ratio	6:1
Operating Temperature	-55 °C to +110 °C
Minimum Shrink Temperature	+120 °C
Softening Point Adhesive	+85 °C
Longitudinal change after shrinkage	-10% max.
Dielectric Strength	20kV/mm according to ASTM D2671
Flammability	not flame retarded



TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Length (L)	Colour	Article-No.
HA67-19.0/3.2	19.0	3.2	3.20	1,220.0	Black (BK)	321-30000
HA67-33.0/5.5	33.0	5.5	3.40	1,220.0	Black (BK)	321-30100
HA67-44.4/7.4	44.4	7.4	3.60	1,220.0	Black (BK)	321-30200
HA67-50.8/8.3	50.8	8.3	4.80	1,220.0	Black (BK)	321-30300
HA67-69.8/11.7	69.8	11.7	4.80	1,220.0	Black (BK)	321-30400
HA67-88.9/17.1	88.9	17.1	4.80	1,220.0	Black (BK)	321-30500
HA67-119.4/22.9	119.4	22.9	4.80	1,220.0	Black (BK)	321-30600
HA67-235.0/40.0	235.0	40.0	4.80	1,220.0	Black (BK)	321-30700

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.