

SPDT RF SWITCH MODEL TWD2206

Package: 14 Pin DIP (DP3)

Also Available in: Connectorized Housings

Features

- 5 - 4000 MHz
- RF1, RF2 Terminated in 'OFF' State
- Integral CMOS Driver
- Operating Temp. - 55 °C to + 85 °C
- Environmental Screening available

Specifications


CHARACTERISTIC	TYPICAL Ta = 25 °C	MIN/MAX Ta = - 55 °C to +85 °C
Frequency	5 - 4000 MHz	5 - 4000 MHz
Insertion Loss (dB)		
5 - 1000 MHz	1.5	1.8 Max.
5 - 2000 MHz	1.9	2.2 Max.
5 - 3000 MHz	2.5	2.8 Max.
Isolation (dB)		
5 - 1000 MHz	65	60 Min.
5 - 2000 MHz	55	50 Min.
5 - 3000 MHz	32	30 Min.
VSWR "ON"/"OFF"		
5 - 1000 MHz	1.25:1	1.5:1 Max.
5 - 2000 MHz	1.6:1	2.0:1 Max.
5 - 3000 MHz	1.6:1	2.0:1 Max.
1 dB Compression (dBm)		
50 MHz	+18.5	+18.0 Min.
500 - 3000 MHz	+24	+22.0 Min.
Switching Speed (nsec) (50% TTL to 90% RF)	40	60 Max.
DC Bias (mA) (4.5 to 5.5 VDC)	0.025	1.0 Max.

Note: Care should always be taken to effectively ground the case of each unit

Maximum Ratings

Ambient Operating Temperature - 55 °C to + 100 °C
 Storage Temperature - 65 °C to + 125 °C
 Case Temperature + 125 °C
 DC Voltage + 6.0 Volts
 Continuous RF Input Power +30 dBm





Pin Layout



Truth Table

Control Input	Switch Position
TTL	RF Common Connected To
0	RF1
1	RF2

Typical Performance Data



Legend ——— + 25 °C - - - - +85 °C · · · · - 55 °C

Amplifonix

2707 Black Lake Place, Philadelphia, PA 19154

TEL 215-464-4000 •••• FAX 215-464-4001