






LOC		DIST		REVISIONS				
FT	0	P	LTR	DESCRIPTION		DATE	DWN	APVD
				J1	REVISED PER ECO-11-004820			



DETAIL A




DETAIL B

- NOTES:
- CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
 - WILL ACCEPT (3) TYPE XII SOCKET CONTACTS.

△ PART NUMBER AND "AMP" INSIGNIA CAN BE LOCATED ON ANY FLANGE EDGE.

4-40 THREADED INSERTS	NO	A	206425-5
.150±.003	YES	A	206425-3
.150±.003	NO	B	206425-2
.150±.003	NO	A	206425-1
C	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BINNER CHK R. STONE APVD —	06/01/94 6-23-94 —	 TE Connectivity	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-10024		NAME RECEPTACLE HOUSING, REVERSE SEX, SHELL SIZE 17, CPC —	
		APPLICATION SPEC		SIZE A1	
	0 PLC ± — 1 PLC ± — 2 PLC ± .005 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH —	WEIGHT —		DRAWING NO 00779	
		CUSTOMER DRAWING		SCALE 2:1	
MATERIAL HOUSING: NYLON, BLACK SEAL: ELASTOMER, GREY				SHEET 1 OF 1	
				REV J1	