






RELIABILITY TEST

ST-03xx Series -P

Note: No voltage is applied to the part during reliability test No. 1~4

Item	Test Conditions	Evaluation Standard
1 Temp. test	(1) High temp. storage life test: The part shall be capable of withstanding a storage temperature of +85°C for 96 hours. (2) Low temp. storage life test: The part shall be capable of withstanding a storage temperature of -40°C for 96 hours. (3) Temp. cycle: The part shall be subjected to 10 cycles. One cycle shall consist of ; 	After the test the part shall meet specifications without any degradation in appearance and performance except SPL. SPL. shall be 87 dB or more.
2 Temp. / Humidity cycle test	The part shall be subjected to 10 cycles. One cycle shall be 8 hours and consist of ;  a, b : 90 ~ 98% RH c : 80 ~ 98% RH	

RELIABILITY TEST

ST-03xx Series -P


Note: No voltage is applied to the part during reliability test No. 1~4

Item		Test Conditions	Evaluation Standard
3	Vibration Test	The part shall be subjected to a vibration cycle of 10Hz to 55Hz to 10Hz in a period of 1 minute. Total peak amplitude shall be 1.52mm(9.3G). The vibration test shall consist of 2 hours per plane in each three mutually perpendicular planes for a total time of 6 hours.	
4	Dropping Test	(1) Fixed drop : The part shall be mounted on 100g jig(standard pcbboard) and dropped from a height of 152cm onto a concrete floor 5 times in each 6 planes. (a total of 30 times.) (2) Free drop : The part only shall be dropped from a height of 75cm onto a 40mm thick wooden board 3 times in 3 axes (X.Y.Z). (a total of 9 times.)	After the test the part shall meet specifications without any degradation in appearance and performance except SPL. SPL. shall be 87 dB or more.
5	Operating life test	(1) Ordinary temperature : The part shall be subjected to 1000 hours at room temperature ($25\pm 10^{\circ}\text{C}$) with rated voltage & resonance frequency applied. (2) High temperature : The part shall be subjected to 500 hours at $+70^{\circ}\text{C}$ with rated voltage & resonance frequency applied. (3) Low temperature : The part shall be subjected to 500 hours at -30°C with rated voltage & resonance frequency applied.	

RELIABILITY TEST

ST-03xx Series -P

Note: No voltage is applied to the part during reliability test No. 1~4

Item		Test Conditions	Evaluation Standard
6	Solderability	The part shall be dipped into the soldering bath conditioned as follows ; Solder temp. : $260 \pm 5^{\circ}\text{C}$ Soaking time : 10 - 11 seconds	95% surface of lead pins must be covered with fresh solder and soldering balls should be found.
7	Pin lead strength	3 lead pins shall be solder on the pc board , and the force (10n) shall be applied behind the part for 10 ± 1 seconds.	
8	For infrared reflow oven	<Recommended temperature profile for reflow oven> (Reference standard ; EIAJ ED-4702) 	After the test the part shall meet specifications without any degradation in appearance and performance except SPL. SPL. shall be 87 dB or more.