

SUBMINATURE TVS ARRAYS

APPLICATIONS

- ✓ Cellular Phones
- ✓ MP3 Players
- ✓ Notebooks & Handheld Devices
- ✓ Personal Digital Assistants (PDAs)
- ✓ Digital Cameras

IEC COMPATIBILITY (EN61000-4)

- ✓ 61000-4-2 (ESD): Air - 15kV, Contact - 8kV
- ✓ 61000-4-4 (EFT): 40A - 5/50ns

FEATURES


- ✓ ESD Protection > 25 kilovolts
- ✓ 200 Watts Peak Pulse Power per Line ($t_d=8/20\mu s$)
- ✓ Low Clamping Voltage & Low Leakage Current
- ✓ Available in 2 Voltages: 5V & 12V
- ✓ Up to Four (4) Lines of Protection

MECHANICAL CHARACTERISTICS

- ✓ Molded JEDEC SC-70-5L
- ✓ Weight 0.14 grams (Approximate)
- ✓ Flammability Rating UL 94V-0
- ✓ 8mm Tape and Reel Per EIA Standard 481-1-A
- ✓ Device Marking: Marking Code



PIN CONFIGURATION





DEVICE CHARACTERISTICS





MAXIMUM RATINGS @ 25°C Unless Otherwise Specified			
PARAMETER	SYMBOL	VALUE	UNITS
Peak Pulse Power ($t_p = 8/20\mu s$) - See Figure 1	P_{PP}	200	Watts
Operating Temperature	T_J	-55°C to 150°C	°C
Storage Temperature	T_{STG}	-55°C to 150°C	°C
Forward Voltage @ 1A, 8/20 μs	V_{FP}	1.5	Volts

ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified							
PART NUMBER	DEVICE MARKING	RATED STAND-OFF VOLTAGE	MINIMUM BREAKDOWN VOLTAGE (See Note 1)	MAXIMUM CLAMPING VOLTAGE (See Fig. 2)	MAXIMUM CLAMPING VOLTAGE (See Fig. 2)	MAXIMUM LEAKAGE CURRENT	MAXIMUM CAPACITANCE
		V_{WM} VOLTS	@ 1mA $V_{(BR)}$ VOLTS	@ $I_p = 1A$ V_C VOLTS	@ 8/20 μs V_C @ I_{PP}	@ V_{WM} I_D μA	0V @ 1 MHz C pF
PSMF05	05	5.0	6.0	9.5	12.0V @ 16.0A	10	175
PSMF12	12	12.0	13.3	15.0	22.0V @ 12.0A	1	75

Note 1: Test between pins 1 to 2, 3 to 2, 4 to 2 and 5 to 2.



GRAPHS



APPLICATION NOTES

The PSMF Series are TVS arrays designed to protect I/O or data lines from the damaging effects of ESD (> 25kv) or EFT. This product provides unidirectional protection, with a surge capability of 200 Watts P_{pp} per line for an 8/20 μ s waveform.

UNIDIRECTIONAL COMMON MODE CONFIGURATION (Figure 1)

The PSMF Series provides up to four (4) lines of protection in a common mode configuration as depicted in Figure 1.


Circuit connectivity is as follows:

- I/O 1 is connected to Pin 1.
- I/O 2 is connected to Pin 3.
- I/O 3 is connected to Pin 4.
- I/O 4 is connected to Pin 5.
- Pin 2 is connected to ground.

CIRCUIT BOARD LAYOUT RECOMMENDATIONS


Circuit board layout is critical for Electromagnetic Compatibility (EMC) protection. The following guidelines are recommended:

- The protection device should be placed near the input terminals or connectors, the device will divert the transient current immediately before it can be coupled into the nearby traces.
- The path length between the TVS device and the protected line should be minimized.
- All conductive loops including power and ground loops should be minimized.
- The transient current return path to ground should be kept as short as possible to reduce parasitic inductance.
- Ground planes should be used whenever possible. For multilayer PCBs, use ground vias.



**Figure 1 - Unidirectional Configuration
Common-Mode I/O Port Protection**

PACKAGE OUTLINE & DIMENSIONS



TAPE & REEL PACKAGING:

Surface mount product is taped and reeled in accordance with EIA-481, reel quantities and sizes are as follows:

7 Inch Reel - 3,000 pieces per reel; 13 Inch Reel - Not Available

ProTek Devices

2929 South Fair Lane, Tempe, AZ 85282

Tel: 602-431-8101 Fax: 602-431-2288

E-Mail: sales@protekdevices.com

Web Site: www.protekdevices.com

COPYRIGHT © ProTek Devices 2001

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice (except JEDEC).

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice, and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance, ProTek assumes no responsibility with respect to the selection or specifications of such products.