




LOC	DIST	REVISIONS					
AR	39	P	LTR	DESCRIPTION	DATE	DWN	APVD
			D3	REVISED PER ECO-12-003620	16FEB2011	RW	SY

D

C

B

A



LATCH FOR POSN SIZES
LESS THEN 16

1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI


1

OBSOLETE

1

OBSOLETE

51.99 [2.047]	80	8-487937-0
46.91 [1.847]	72	7-487937-2
39.29 [1.547]	60	6-487937-0
32.94 [1.297]	50	5-487937-0
29.13 [1.147]	44	4-487937-4
26.59 [1.047]	40	4-487937-0
22.78 [.897]	34	3-487937-4
20.24 [.797]	30	3-487937-0
17.70 [.697]	26	2-487937-6
16.43 [.647]	24	2-487937-4
13.89 [.547]	20	2-487937-0
11.35 [.447]	16	1-487937-6
10.08 [.397]	14	1-487937-4
8.81 [.347]	12	1-487937-2
7.54 [.297]	10	1-487937-0
6.27 [.247]	8	487937-8
64.69 [2.547]	100	487937-1
A	NO OF POSN	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 02/08/91	 TE Connectivity			
DIMENSIONS: mm[INCHES]		CHK J. McCLINTON 3-5-91				
		APVD D.L. ROCKER 3-6-91	NAME HOUSING, RCPT, .050 , FFC			
		PRODUCT SPEC				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC				
0 PLC ± -		—				
1 PLC ± -		—				
2 PLC ± 0.13 [.005]		—				
3 PLC ± -		—				
4 PLC ± -		—				
ANGLES ± ± -		—				
FINISH		—				
MATERIAL POLYESTER BLACK		WEIGHT —				
		CUSTOMER DRAWING				
		SCALE 4:1	SHEET 1 of 1		REV D3	