



Relay Characteristics

	CPC1335P	Units
Blocking Voltage	350	V
Load Current	100	mA
Max R_{ON}	35	Ω
LED Current to Operate	1.0	mA

Transient Protection Characteristics

Part Number	Peak Pulse Power	V_{WM}
CPC1335P	600W	40.2V

Features

- Small 8 Pin Surface Mount Package
- Low Drive Power Requirements (TTL/CMOS Compatible)
- No Moving Parts
- High Reliability
- Arc-Free With No Snubbing Circuits
- 3750V_{RMS} Input/Output Isolation
- No EMI/RFI Generation
- Machine Insertable, Wave Solderable
- Tape & Reel Version Available

Applications

- Security
- Aerospace
- Industrial Controls

Description

CPC1335P is a 1 Form-A solid state relay with Bi-directional TVS relay protection. The efficient MOSFET switches and photovoltaic die that use Clare's patented OptoMOS® architecture to provide 3750 V_{RMS} of input to output isolation. The optically coupled input is controlled by highly efficient GaAlAs infrared LEDs. The device is available in an 8 pin space saving surface mount package. The transient voltage suppressor is designed to meet the requirements of EN50130-4 (installation class 3).

Approvals


- UL pending.

Ordering Information


Part #	Description
CPC1335P	8 Pin Flatpack (50/Tube)
CPC1335PTR	8 Pin Flatpack (1000/Reel)

Pin Configuration

CPC1335P Pinout



Switching Characteristics of Normally Open (Form A) Devices



**CPC1335P****Absolute Maximum Ratings - Relay (@ 25° C)**

Parameter	Min	Typ	Max	Units
Input Power Dissipation	-	-	150 ¹	mW
Input Control Current	-	-	50	mA
Peak (10ms)	-	-	1	A
Reverse Input Voltage	-	-	5	V
Total Power Dissipation	-	-	800 ²	mW
Blocking Voltage	-	-	350	V
Isolation Voltage Input to Output	3750	-	-	V _{RMS}
Operational Temperature	-40	-	+85	°C
Storage Temperature	-40	-	+125	°C
Soldering Temperature (10 Seconds Max.)	-	-	+220	°C

¹ Derate Linearly 1.33 mW/°C² Derate Linearly 6.67 mW/°C**Absolute Maximum Ratings**

Absolute Maximum Ratings	Symbol	Max	Units
Peak Pulse Power (I _{pp} =9.3A, 10/1000µs pulse)	P _{PP}	600	W
Max Stand-Off/Working Voltage	V _{WM}	40.2	V













Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at these or any other conditions beyond those indicated in the operational sections of this data sheet is not implied. Exposure of the device to the absolute maximum ratings for an extended period may degrade the device and effect its reliability.

Electrical Characteristics: Relay

Parameter	Conditions	Symbol	Min	Typ	Max	Units
Output Characteristics @ 25°C						
Load Current (Continuous) AC Peak ¹	I _F =2mA	I _L	-	-	100	mA
Peak Load Current	10ms max	I _{LPK}	-	-	350	mA
On-Resistance ²	I _L =100mA	R _{ON}	-	25	35	Ω
Off-State Leakage Current	V _L =350V	I _{LEAK}	-	-	1	µA
Switching Speeds						
Turn-On	I _F =2mA, V _L =10V	T _{ON}	-	-	10	ms
Turn-Off	I _F =2mA, V _L =10V	T _{OFF}	-	-	10	ms
Output Capacitance	50V _{RMS} ; f=1MHz	C _{OUT}	-	25	-	pF
Input Characteristics @ 25°C						
Input Control Current ³	I _L =100mA	I _F	1	-	50	mA
Input Voltage Drop	I _F =5mA	V _F	0.9	1.2	1.4	V
Reverse Input Current	V _R =5V	I _R	-	-	10	µA
Input to Output Capacitance	-	C _{I/O}	-	3	-	pF

¹ Load current derates linearly from 100 mA @ 25°C to 70mA @ 85°C² Measurement taken within 1 second of on time³ For applications requiring high temp operation (greater than 60°C) a minimum LED drive current of 3mA is recommended.**Electrical Characteristics: TVS**

Parameter	Conditions	Symbol	Min	Typ	Max	Units
Clamping Voltage	(I _{pp} =9.3A)	V _C	-	-	64.8	V
Reverse Breakdown Voltage	(I _{BR} =1000 µA)	V _{BR}	44.4	-	-	V
Reverse Leakage Current	(V _{WM} =40.2 V)	I _D	-	-	5	µA




PERFORMANCE DATA*


*The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.



CPC1335P


PERFORMANCE DATA*




*The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.

MECHANICAL DIMENSIONS


8 Pin Flatpack ("P" Suffix)



PC Board Pattern (Top View)



Tape and Reel Packaging for 8 Pin Flatpack Package



Dimensions
mm
(inches)



CLARE

For additional information please visit our website at: www.clare.com

Clare, Inc. makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to make changes to specifications and product descriptions at any time without notice. Neither circuit patent licenses nor indemnity are expressed or implied. Except as set forth in Clare's Standard Terms and Conditions of Sale, Clare, Inc. assumes no liability whatsoever, and disclaims any express or implied warranty, relating to its products including, but not limited to, the implied warranty of merchantability, fitness for a particular purpose, or infringement of any intellectual property right.

The products described in this document are not designed, intended, authorized or warranted for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or where malfunction of Clare's product may result in direct physical harm, injury, or death to a person or severe property or environmental damage. Clare, Inc. reserves the right to discontinue or make changes to its products at any time without notice.

Specification: DS-CPC1335P-R2.0
©Copyright 2002, Clare, Inc.
OptoMOS® is a registered trademark of Clare, Inc.
All rights reserved. Printed in USA.
11/19/02