





VIEW SHOWING SWIVEL ACTION



CONDUCTOR RANGE										
MIN. RUN	MIN. TAP	MAX. RUN & TAP	CAT. NO.	H	J	L	T	W	REV.	
#2 STR. (.292 DIA.)	#6 SOL. (.162 DIA.)	2/0 STR. (.418 DIA.)	KVSW26	1.76	.31	1.04	.12	1.56	12	
1/0 STR. (.373 DIA.)	#6 SOL. (.162 DIA.)	4/0 STR. (.528 DIA.)	KVSW28	2.50	.38	1.04	.28	1.67	10	
250 MCM (.575 DIA.)	#4 SOL. (.204 DIA.)	350 MCM (.681 DIA.)	KVSW31	2.80	.50	1.62	.25	2.25	10	
400 MCM (.728 DIA.)	#4 STR. (.232 DIA.)	500 MCM (.813 DIA.)	KVSW34	3.06	.50	1.34	.28	2.20	10	
400 MCM (.728 DIA.)	4/0 STR. (.528 DIA.)	800 MCM (1.031 DIA.)	KVSW40	3.47	.50	2.31	.28	2.72	11	
500 MCM (.813 DIA.)	250 MCM (.575 DIA.)	1000 MCM (1.152 DIA.)	KVSW44	4.14	.62	2.56	.31	3.09	10	

MATERIAL:-
CAST COPPER ALLOY

REFERENCE:-
FD26217

NOTES:

1 KVSW28 AND KVSW34 ONLY HAVE NO SERRATIONS.

RUN	MIN. TAP
800 - 650 MCM	4/0
600 MCM	250 MCM
500 MCM	350 MCM
450 MCM	450 MCM
400 MCM	500 MCM

3 STANDARD BOLT MATERIAL IS DURIUM (SILICON BRONZE) OPTIONAL, SAME SIZE, 18-8 STAINLESS STEEL AND GALVANIZED STEEL BOLTS ARE ALSO AVAILABLE. SPECIFY -SS OR -GS RESPECTIVELY, ON END OF CATALOG NUMBER FOR OPTIONAL BOLTS.

17	9-20-81	ADDED NOTE 3 (D.C. 2027B)	JEL	KH	SUPERSEDES:- SD9323-9
16	8-31-88	SEE REV. REF. PRINT (ECP 4632)	WS	H.C.	SERVICE CONNECTOR
15	2-4-82	2/0 STR, 500 MCM WAS .418, .814 (DC10740)	CA/L	AM	CAT. NO. KVSW (GEN'L.)
14	2-5-70	REFERENCE TO SUPPL. WAS REMOVED (DC6142)	JRH	JPS	DRAWN 4-2-52 W.K. CHECKED 4-5-52 C.H.JR.
13	2-5-65	REV. REF. PRINT (E.C. 31073)	T.E.D	MJM	BURNDY Corporation
12	6-3-63	NOTE 3 ADDED (E.C. 17571)	T.A.L.	ERD	NORWALK, CONNECT.
11	5-17-62	NOTE 2 ADDED APP. 11.3, (E.C. 17234)	JAA	ERD	DRAWING NO. SD9323
10	4-28-61	REPRODUCED WITHOUT CHANGE PER A.K.K.	JAA	ERD	REV. 17
REV.	DATE	REVISION DESCRIPTION	BY	CKD.	