


F/SWB-24

Technische Daten Techn. Terms	Bedingungen Conditions	Wert Value
Betriebsspannungsbereich <i>Operating Voltage</i>	DC	16...30 V
Nennspannung <i>rated Voltage</i>	DC	24 V
Max. Stromaufnahme <i>Current Consumption</i>	bei Nennspannung <i>at rated voltage</i>	20 mA
Lautstärke <i>SPL</i> bei Nennspannung <i>at rated voltage</i>	Abstand <i>Distance</i> 10 cm	80 dB
Frequenzbereich <i>Frequency Range</i>		400 $\pm$ 100 Hz
Reaktionszeit <i>Response time</i>		$\leq$ 330 msec
Betriebstemperatur <i>Operating Temperature</i>		- 40... + 80 °C
Lagertemperatur <i>Storage temperature</i>		- 40... + 80 °C
Gewicht <i>weight</i>		10 g

Zeichnungen *Drawings*



DIGISOUND

Halbzeug, Werkstoff

Untolerierte Maße

Zeichn.-Nr.

951101.6B

Maßstab

Ersatz f.
Zeichn.

Page/Blatt 1 von 2

	Tag	Name	And. zust.	And.-Mittlg. Nr.	Tag	Name
gezeichnet						
bearbeitet	28.01.97	Bär				
geprüft	29.01.97	Kub				
normgepr.						

F/SWB-24

Diese Zeichnung ist unser Eigentum. Vervielfältigung unbefugte Verwertung, Mitteilung an andere ist strafbar und Schadensersatzpflichtig

Vervielfält.-Pause
Nr.

Arbeitspause Nr.

Reliability test

ITEM	METHOD OF TEST	STANDARD
Storage in high temp.	Storage in + 80°C test box for 96 hours, then expose to the room temperature for 2 hours without applying power.	All specifications must be satisfied in this condition.
Storage in low temp.	Storage in – 30°C test box for 96 hours, then expose to the room temperature for 2 hours without applying power.	All specifications must be satisfied in this condition.
Life test in the room temp.	Operate continuously for 1000 hours with applying rated voltage.	All specifications must be satisfied in this condition.
Life test in high temp.	Operate continuously in + 80°C for 500 hours applying 30 V.	All specifications must be satisfied in this condition.
Life test in low temp.	Operate continuously in – 30°C for 500 hours applying 16 V.	All specifications must be satisfied in this condition.
Temperature cycle test	Make this test for 5 cycles without applying power, the expose to the room temperature for 2 hours.	All specifications must be satisfied in this condition.
Humidity cycle test	Make this test for 5 cycles without applying power, the expose to the room temperature for 2 hours.	All specifications must be satisfied in this condition.
Vibration test	Make this test for the directions of X,Y and Z for 2 hours each (total 6 hours). To-and-fro sweep times 1 minute.	All specifications must be satisfied in this condition.
Drop test	Drop a buzzer naturally from the height of 700mm to the surface of 10mm thick woodenboard. Three directions (x, y & z).	All specifications must be satisfied in this condition.
Solderability test	Soldering Temperature: 230°C Heat applying time: 3 sec.	

Diese Zeichnung ist unser Eigentum. Vervielfältigung unbefugte Verwertung, Mitteilung an andere ist strafbar und Schadensersatzpflichtig

		Halbzeug, Werkstoff		Untolerierte Maße		Zeichn.-Nr. 951101.6B	
				Maßstab		Ersatz f. Zeichn. Page/Blatt 2 von 2	
	Tag	Name	And. zust.	And.-Mittlg. Nr.	Tag	Name	F/SWB-24
gezeichnet							
bearbeitet	28.01.97	Bär					
geprüft	29.01.97	Kub					
normgepr.							

Vervielfält.-Pause Nr.

Arbeitspause Nr.