




Revisions



NOTE: FOR MOUNTING
MAX BOLT DIA. 1/2"



PANEL-TRAN

Type No.

KVA	CATALOG NUMBER	VOLTAGE		Stainless Steel	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
5	PT06-1150005-SS	480	120/240	304	120 Lbs	1	60 Hz

TYPICAL PERFORMANCE DATA

Winding Rise	115°C
Insulation	180°C
Sound Level	40 dB

120 V (1-Pole)	8
-------------------	---

240 V (2-Pole)	4
-------------------	---

Typical Efficiency	
Full Load Losses	
No Load Losses	

A	B	C	D	E	F	G	H	J	K	L	M	N		
32.13	13.25	7.63	30.63	7.06	10.31	27.81	1.50	3.00	3.00	17.25	10.06	2.63		

					A	PRINTS TO	CONTROL 7	PT06-1150005-SS
--	--	--	--	--	----------	-----------	---------------------	------------------------