

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0038002096

Status:

Active

Overview:

kk

Description:

2.54mm (.100") KK® IDT Double Cantilever Contact, 6 Circuits, Tin (Sn), Feed-Through, Friction Ramp and Polarizing Rib, Brown ID Stripe

Documents:

3D Model

Drawing (PDF)

Product Specification PSX-7690S (PDF)

Packaging Specification PK-7720-100 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

IDT and Solder Connectors

Series

7720

Comments

Version J

Crimp Quality Equipment

Yes

Overview

kk

Product Name

KK®

Physical

Circuits (Loaded)

6

Circuits (maximum)

6

Color - Resin

Natural

Durability (mating cycles max)

5

Flammability

94V-2

Gender

Female

Glow-Wire Compliant

No

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

2.54mm (.100")

Pitch - Termination Interface

2.54mm (.100")

Polarized to Mating Part

Yes

Stackable

No

Temperature Range - Operating

0°C to +50°C

Termination Interface: Style

IDT or Pierce

Wire Size AWG

26 Stranded, 28 Solid, 28 Stranded Topcoat

Electrical

Current - Maximum per Contact

4A

Voltage - Maximum

250V

Material Info

Old Part Number

7720SC06J

Reference - Drawing Numbers

Packaging Specification

PK-7720-100

Product Specification

PSX-7690S

Sales Drawing

SDA-7720S-*N*



image - Reference only

Series

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

7720Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Insertion Tool for 2.54mm (.100") Pitch KK® IDT Crimp Terminals	0638133504

This document was generated on 09/19/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[38-00-2096](#)