



2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NUMBER*	MAXIMUM CABLE DIA. in. (mm)	WEIGHT lbs. (g)/100pcs
LWC19-A	0.19 (4.8)	0.29 (130)

NOTES:

*1) SEE <http://www.panduit.com>
FOR PART NUMBER SUFFIX DESIGNATION,
FOR PACKAGE SIZE.

2) MOUNT IS DESIGNED TO SUPPORT
0.25 lbs (113.4g) MAX WEIGHT ON
A CLEAN DRY SMOOTH SURFACE.

TO APPLY LATCHING WIRE CLIP:
1. REMOVE PROTECTIVE LINER
2. PLACE IN DESIRED LOCATION
3. APPLY PRESSURE TO TOP OF
LATCHING WIRE CLIP



ADHESIVE BACKING: PRESSURE SENSITIVE FOAM
0.04 [1.0] THICK WITH PROTECTIVE LINER TO
EXTEND BEYOND EDGE FORMING A TEAR TAB.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT
WITH RESPECT TO ADHESIVE BOND PERFORMANCE, AMONG
OTHER THINGS, THE CONDITIONS UNDER WHICH THESE
MOUNTS MAY BE APPLIED, AND/OR THE SURFACE TO WHICH
THEY MAY BE APPLIED, ARE BEYOND PANDUIT'S CONTROL.

DIMENSIONS IN BRACKETS ARE METRIC (mm)

A

A

TITLE						LWC19-A, LATCHING WIRE CLIP			
ITEM REVISION NAME						CUSTOMER DRAWING			
DATASET FILE NAME						10B015EQ/02			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)						PANDUIT			
.x ± 0.05 [1.3] .xxx ± 0.010 [0.25] .xx ± 0.02 [0.5] ANGLES ± 5°						MATERIAL: NYLON 6/6			
THIRD ANGLE PROJECTION						DRAWING NUMBER: GB0239EH			
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE A			
AJV	9-20-96		2X						

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	8/05/13	BWG	MPH	RTF	REVISED MAX. CABLE DIA. SEE ECN FOR DETAILS.	GB0239EH/03
3	8/05/13	BWG	MPH	RTF	AND REVISED TITLE BORDER.	GB0239EH/03

2

1

D101000A/16