




LOC		DIST		REVISIONS						
FT		0		P	LTR	DESCRIPTION	DATE	DWN	APVD	
					A	RELEASED	29JUN2001	SW	DB	
					B	REVISED EC 063B-0357-01	10JUL2001	SW	DB	



796895-3 AS SHOWN

- △ MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR: GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
2. SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
3. END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.
4. WIRE SIZE RANGE: 12-30 AWG.
5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC., FILE N° E60677.
6. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
- △ NOT CUMULATIVE TOLERANCE.



RECOMMENDED PC BOARD LAYOUT

37.5	5	796895-5
30.0	4	796895-4
22.5	3	796895-3
15.0	2	796895-2
A	NO. OF POSN	PART NUMBER

THIS DRAWING IS UNPUBLISHED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED IN THE ORDER. IT IS TO BE RETURNED TO TYCO ELECTRONICS CORPORATION WHEN NO LONGER REQUIRED FOR THE LATEST EDITION.		DWN S. WELDON 09JUL2001	Tyco Electronics Harrisburg, PA 17105-3608		
DIMENSIONS:		CHK D. BIEVENOUR 09JUL2001	NAME BUCHANAN		
mm		APVD D. BIEVENOUR 09JUL2001	PRODUCT SPEC TERMINAL BLOCK, PCB MOUNT, TOP WIRE ENTRY, STACKING, ALIGNED SCREW AND PIN, 7.5mm PITCH		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC			
0 PLC ±.1		SIZE			
1 PLC ±0.1		CAGE CODE			
2 PLC ±0.25		DRAWING NO			
3 PLC ±0.000		RESTRICTED TO			
4 PLC ±0.0000		A 00779 C-796895			
ANGLES		WEIGHT			
FINISH		CUSTOMER DRAWING			
MATERIAL		SCALE 6:1			
		SHEET 1 OF 1			
		REV B			