


© COPYRIGHT 1997 BY SPC TECHNOLOGY.
ALL RIGHTS RESERVED. NO PORTION OF
THIS PUBLICATION, WHETHER IN WHOLE
OR IN PART CAN BE REPRODUCED
WITHOUT THE EXPRESS WRITTEN CONSENT
OF SPC TECHNOLOGY.

REVISIONS

DOC. NO. SPC-FD04, Total Pages: 2
Effective: 7/15/97, DCP No: 229 Supersedes DCP No: 103

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
162	A	RELEASED	J.W.M.	1/7/98	J.C.	2/4/98	B.B.	2/5/98



Electrical Characteristics
Voltage Rating: 250VDC
Current Rating:

UL @ 6A: 115/250VAC
CSA @ 6A: 115/250VAC
VDE @ 10A: 250VAC

Note: power switch VDE approved c
Voltage selector switch UL/CSA/VDE
5A/250VAC.

Operating Frequency: 48-440Hz

HiPot Rating (for one minute)


Line to ground: 2000VAC

line to line: 1500VAC

Minimum Insulation Res. (For 1 min. @ 500 VDC)

Line to ground: 10M Ohm

Line to line: 10M Ohm



SPC-FD04-DWG

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION
AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE
BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE
INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

Unless Otherwise Specified:
Dimensions are shown for
reference only!

DRAWN BY:	DATE:
Jeff McVicker	1/7/98
CHECKED BY:	DATE:
JOHN COLE	2/4/98
APPROVED BY:	DATE:
BRETT BRAATZ	2/5/98

DRAWING TITLE:

Mult-Function Module

SIZE DWG. NO.

A

2164

ELECTRONIC FILE

92N4167.dwg

REV

A

SCALE: NTS

U.O.M.: INCHES [mm]

SHEET: 1 OF 1