



## **Aluminum electrolytic capacitors**

Axial-lead and soldering star capacitors

**Series/Type:** B41692, B41792



**Date:** November 2012

## Applications

- Automotive electronics

## Features

- Long useful life, 2000 h at up to 140 °C
- High ripple current capability
- Compact design
- High vibration stability
- Shelf life up to 15 years at storage temperatures up to 40 °C.  
To ensure solderability, the capacitors should be built into the application within one year of delivery. After a total of two years' storage, the operating voltage must be applied for one hour to ensure the specified leakage current.
- RoHS-compatible



## Construction


- Charge/discharge-proof, polar
- Aluminum case with insulating sleeve
- Negative pole connected to case

## Terminals

- Axial leads, welded to ensure perfect electrical contact
- Soldering star for upright mounting on PCB available
- Alternative axial-lead design with double-sided plates for horizontal mounting available upon request

## Taping and packing

- Axial-lead capacitors will be delivered in pallet package  
Capacitors with  $d \times l \leq 16 \times 30$  mm are also available taped on reel
- Soldering star capacitors are packed in cardboard




## Specifications and characteristics in brief

Rated voltage $V_R$	25 ... 63 V DC						
Surge voltage $V_S$	$1.15 \cdot V_R$						
Rated capacitance $C_R$	220 ... 6800 $\mu\text{F}$						
Capacitance tolerance	-10/+30% $\triangle Q$						
Leakage current $I_{\text{leak}}$ (5 min, 20 °C)	$I_{\text{leak}} \leq 0.006 \mu\text{A} \cdot \left( \frac{C_R}{\mu\text{F}} \cdot \frac{V_R}{\text{V}} \right) + 4 \mu\text{A}$						
Self-inductance ESL <sup>1)</sup>	Diameter d (mm)		12	14	16	18	20/21
	Terminals	Length l (mm)	Approx. ESL (nH)				
	axial	25	—	22	—	30	—
		29	—	—	—	—	38
		30	21	24	29	34	—
		35	—	—	31	—	—
		39	—	—	33	38	45
		49	—	—	—	—	50
	soldering star	25	—	6	—	8	—
		30	6	7	8	10	—
		35	—	—	9	—	—
		39	—	—	9	11	13
		49	—	—	—	—	14
Useful life <sup>2)</sup>			Requirements:				
150 °C; $V_{\text{op}}$ ; $0.5 \cdot I_{\text{AC,R}}^{3)}$	> 2000 h		$\Delta C/C \leq \pm 30\%$ of initial value				
140 °C; $V_R$ ; $0.6 \cdot I_{\text{AC,R}}$	> 2000 h		$\text{ESR} \leq 3$ times initial specified limit <sup>4)</sup>				
125 °C; $V_R$ ; $I_{\text{AC,R}}$	> 5000 h		$I_{\text{leak}} \leq$ initial specified limit				
85 °C; $V_R$ ; $I_{\text{AC,max}}$	> 15000 h						
40 °C; $V_R$ ; $2 \cdot I_{\text{AC,R}}$	> 500000 h						
Voltage endurance test			Post test requirements:				
125 °C; $V_R$	2000 h		$\Delta C/C \leq \pm 10\%$ of initial value				
			$\text{ESR} \leq 1.3\%$ initial specified limit <sup>4)</sup>				
			$I_{\text{leak}} \leq$ initial specified limit				
Vibration resistance test	To IEC 60068-2-6, test Fc: Frequency range 10 Hz ... 2 kHz, displacement amplitude max. 1.5 mm, acceleration max. 20 g, duration 3 $\times$ 2 h. Capacitor mounted by its wire leads at a distance of (6 $\pm$ 1) mm from the case and additionally clamped by the case.						
IEC climatic category	To IEC 60068-1: 55/125/56 (-55 °C/+125 °C/56 days damp heat test)						
Detail specification	Similar to CECC 30301-802						
Sectional specification	IEC 60384-4						

1) If optimum circuit design is used, the values are lower by 30%.


2) Refer to chapter "General technical information, 5 Useful life" on how to interpret useful life.

3)  $V_{\text{op}}$ : see useful life graph4)  $\text{ESR}_{\text{max}}$  at 100 Hz, 20 °C



B41692, B41792


Compact – up to 140 °C

**B41692, Axial-lead capacitors****Dimensional drawing****Dimensions, weights and packing units**

$d \times l$ mm	$d_{\max} \times l_{\max}$ mm	Approx. weight g	Packing units (pcs.)	
			Pallet	Reel
12 × 30	12.5 × 30.5	5.1	288	450
14 × 25	14.5 × 25.5	5.7	200	350
14 × 30	14.5 × 30.5	6.8	200	350
16 × 30	16.5 × 30.5	8.9	180	250
16 × 35	16.5 × 35.5	10.4	180	—
16 × 39	16.5 × 40	11.7	180	—
18 × 25	18.5 × 25.5	9.3	160	—
18 × 30	18.5 × 30.5	11.1	160	—
18 × 39	18.5 × 40	14.7	160	—
20 × 29	20.5 × 29.5	13.5	140	—
21 × 39	21.5 × 40	20.0	140	—
21 × 49	21.5 × 50	25.0	110	—

B41692, B41792


Compact – up to 140 °C




## B41792, Soldering star capacitors

### Dimensional drawings

Mounting holes d = 12 mm ... 14 mm




Mounting holes d = 16 mm ... 21 mm



### Dimensions, weights and packing units

d × l mm	d <sub>max</sub> × l <sub>max</sub> mm	c ± 0.1 mm	e ± 0.1 mm	Approx. weight g	Packing units pcs.
12 × 30	13.5 × 32	12.5	3.0	5.4	480
14 × 25	15.5 × 27	14.5	3.0	6.1	480
14 × 30	15.5 × 32	14.5	3.0	7.2	480
16 × 30	17.5 × 32	16.5	3.0	9.4	300
16 × 35	17.5 × 37	16.5	3.0	10.9	200
16 × 39	17.5 × 41.5	16.5	3.0	12.2	200
18 × 25	19.5 × 27	18.5	3.0	9.9	300
18 × 30	19.5 × 32	18.5	3.0	11.8	300
18 × 39	19.5 × 41.5	18.5	3.0	15.4	200
21 × 39	22.5 × 41.5	21.5	3.5	21.0	324
21 × 49	22.5 × 51.5	21.5	3.5	26.0	264



B41692, B41792


Compact – up to 140 °C

### Overview of available types

$V_R$ (V DC)	25	40	63
Case dimensions d × l (mm)			
$C_R$ ( $\mu$ F)			
220			12 × 30
330			14 × 30
470		12 × 30	16 × 30
680	12 × 30	14 × 30	16 × 39 18 × 30
1000	14 × 25	16 × 30	18 × 39
1100			20 × 29
1200		16 × 35	
1500	14 × 30	16 × 39 18 × 30	
1800	18 × 25		21 × 39
2200	16 × 39 18 × 30	18 × 39 20 × 29	21 × 49
3300	18 × 39 20 × 29	21 × 39	
4400		21 × 49	
5000	21 × 39		
6800	21 × 49		


B41692, B41792

Compact – up to 140 °C



### Case dimensions and ordering codes

$V_R$ V DC	$C_R$ 100 Hz 20 °C μF	Case dimensions $d \times l$ mm	Ordering code Axial pallet	Ordering code Axial reel	Ordering code Soldering star
25	680	12 x 30	B41692A5687Q001	B41692A5687Q003	B41792A5687Q001
	1000	14 x 25	B41692A5108Q001	B41692A5108Q003	B41792A5108Q001
	1500	14 x 30	B41692A5158Q001	B41692A5158Q003	B41792A5158Q001
	1800	18 x 25	B41692A5188Q001		B41792A5188Q001
	2200	16 x 39	B41692A5228Q001		B41792A5228Q001
	2200	18 x 30	B41692B5228Q001		B41792B5228Q001
	3300	18 x 39	B41692A5338Q001		B41792A5338Q001
	3300	20 x 29	B41692B5338Q001		
	5000	21 x 39	B41692A5508Q001		B41792A5508Q001
	6800	21 x 49	B41692A5688Q001		B41792A5688Q001
40	470	12 x 30	B41692A7477Q001	B41692A7477Q003	B41792A7477Q001
	680	14 x 30	B41692A7687Q001	B41692A7687Q003	B41792A7687Q001
	1000	16 x 30	B41692A7108Q001	B41692A7108Q003	B41792A7108Q001
	1200	16 x 35	B41692A7128Q001		B41792A7128Q001
	1500	16 x 39	B41692A7158Q001		B41792A7158Q001
	1500	18 x 30	B41692B7158Q001		B41792B7158Q001
	2200	18 x 39	B41692A7228Q001		B41792A7228Q001
	2200	20 x 29	B41692B7228Q001		
	3300	21 x 39	B41692A7338Q001		B41792A7338Q001
	4400	21 x 49	B41692A7448Q001		B41792A7448Q001
63	220	12 x 30	B41692A8227Q001	B41692A8227Q003	B41792A8227Q001
	330	14 x 30	B41692A8337Q001	B41692A8337Q003	B41792A8337Q001
	470	16 x 30	B41692A8477Q001	B41692A8477Q003	B41792A8477Q001
	680	16 x 39	B41692A8687Q001		B41792A8687Q001
	680	18 x 30	B41692B8687Q001		B41792B8687Q001
	1000	18 x 39	B41692A8108Q001		B41792A8108Q001
	1100	20 x 29	B41692A8118Q001		
	1800	21 x 39	B41692A8188Q001		B41792A8188Q001
	2200	21 x 49	B41692A8228Q001		B41792A8228Q001



B41692, B41792

Compact – up to 140 °C

## Technical data

$C_R$ 100 Hz 20 °C $\mu F$	Case dimensions d × l mm	ESR <sub>max</sub> 100 Hz 20 °C	ESR <sub>max</sub> 100 Hz –40 °C	ESR <sub>max</sub> 10 kHz 20 °C	Z <sub>max</sub> 100 kHz 20 °C	I <sub>AC,max</sub> 10 kHz 105 °C	I <sub>AC,max</sub> 10 kHz 125 °C	I <sub>AC,R</sub> 10 kHz 125 °C	I <sub>AC,max</sub> 10 kHz 140 °C
-------------------------------------	-----------------------------------	---------------------------------------	--	---------------------------------------	--------------------------------------	---	---	---------------------------------------	---

 $V_R = 25$  V DC

680	12 × 30	250	1600	165	155	3.8	2.85	1.95	1.25
1000	14 × 25	170	1200	120	112	4.1	3.1	2.1	1.4
1500	14 × 30	120	800	82	77	5.3	4.0	2.75	1.8
1800	18 × 25	100	700	75	70	6.3	4.7	3.2	2.1
2200	16 × 39	82	550	55	50	7.9	5.9	4.05	2.6
2200	18 × 30	79	550	52	48	7.8	5.8	4.0	2.6
3300	18 × 39	53	360	35	33	10.8	8.1	5.5	3.6
3300	20 × 29	55	360	38	36	9.1	6.8	4.6	3.0
5000	21 × 39	37	240	27	27	12.9	9.6	6.6	4.3
6800	21 × 49	28	180	20	20	16.3	12.1	8.3	5.4

 $V_R = 40$  V DC




470	12 × 30	240	1400	135	128	4.2	3.1	2.15	1.4
680	14 × 30	170	1000	95	90	5.1	3.8	2.6	1.7
1000	16 × 30	120	660	70	67	5.9	4.4	3.0	2.0
1200	16 × 35	95	550	55	53	7.2	5.3	3.6	2.4
1500	16 × 39	80	450	50	48	8.2	6.1	4.2	2.7
1500	18 × 30	77	450	45	43	8.3	6.1	4.2	2.7
2200	18 × 39	53	300	30	29	11.4	8.5	5.8	3.8
2200	20 × 29	55	300	33	32	9.3	6.9	4.8	3.1
3300	21 × 39	39	200	23	23	13.1	9.8	6.7	4.4
4400	21 × 49	30	160	18	18	16.6	12.3	8.5	5.5

 $V_R = 63$  V DC


220	12 × 30	350	1600	145	138	4.0	3.0	2.05	1.35
330	14 × 30	240	1100	100	95	5.0	3.7	2.55	1.7
470	16 × 30	170	750	75	72	5.8	4.3	3.0	2.0
680	16 × 39	120	500	55	53	8.0	6.0	4.1	2.7
680	18 × 30	114	500	50	48	8.0	6.0	4.1	2.7
1000	18 × 39	78	350	35	34	11.1	8.2	5.7	3.7
1100	20 × 29	75	330	36	35	9.3	6.9	4.8	3.1
1800	21 × 39	47	220	23	23	13.2	9.8	6.7	4.4
2200	21 × 49	38	175	19	19	16.5	12.3	8.5	5.5

B41692, B41792

Compact – up to 140 °C



**Useful life<sup>1)</sup>**depending on ambient temperature  $T_A$  under ripple current operating conditions at  $V_R$ **Useful life<sup>1)</sup>**depending on case temperature  $T_C$  under ripple current operating conditions at  $V_R$ 

1) Refer to chapter "General technical information, 5 Useful life" on how to interpret useful life.



B41692, B41792


Compact – up to 140 °C

**Useful life<sup>1)</sup>**depending on ambient temperature  $T_A$  under ripple current operating conditions at  $V_{op}$  $V_R = 25 \text{ V}$ :  $V_{op} \leq 20 \text{ V}$ ; $V_R = 40 \text{ V}$ :  $V_{op} \leq 35 \text{ V}$ ; $V_R = 63 \text{ V}$ :  $V_{op} \leq 55 \text{ V}$ **Useful life<sup>1)</sup>**depending on case temperature  $T_C$  under ripple current operating conditions at  $V_{op}$  $V_R = 25 \text{ V}$ :  $V_{op} \leq 20 \text{ V}$ ; $V_R = 40 \text{ V}$ :  $V_{op} \leq 35 \text{ V}$ ; $V_R = 63 \text{ V}$ :  $V_{op} \leq 55 \text{ V}$ 


1) Refer to chapter "General technical information, 5 Useful life" on how to interpret useful life.

B41692, B41792

Compact – up to 140 °C




### Frequency factor of permissible ripple current $I_{AC}$ versus frequency $f$




### Frequency characteristics of ESR


Typical behavior




### Equivalent series resistance ESR versus frequency $f$

Typical behavior for 2200  $\mu$ F/25 V

### Impedance $Z$ versus frequency $f$

Typical behavior for 2200  $\mu$ F/25 V

**B41692, B41792****Compact – up to 140 °C**

## Cautions and warnings

### Personal safety

The electrolytes used by EPCOS have been optimized both with a view to the intended application and with regard to health and environmental compatibility. They do not contain any solvents that are detrimental to health, e.g. dimethyl formamide (DMF) or dimethyl acetamide (DMAC).

Furthermore, some of the high-voltage electrolytes used by EPCOS are self-extinguishing.


As far as possible, EPCOS does not use any dangerous chemicals or compounds to produce operating electrolytes. However, in exceptional cases, such materials must be used in order to achieve specific physical and electrical properties because no alternative materials are currently known. However, the amount of dangerous materials used in our products is limited to an absolute minimum.

Materials and chemicals used in EPCOS aluminum electrolytic capacitors are continuously adapted in compliance with the EPCOS Corporate Environmental Policy and the latest EU regulations and guidelines such as RoHS, REACH/SVHC, GADSL, and ELV.

MDS (Material Data Sheets) are available on the EPCOS website for all types listed in the data book. MDS for customer specific capacitors are available upon request.

MSDS (Material Safety Data Sheets) are available for all of our electrolytes upon request.


Nevertheless, the following rules should be observed when handling aluminum electrolytic capacitors: No electrolyte should come into contact with eyes or skin. If electrolyte does come into contact with the skin, wash the affected areas immediately with running water. If the eyes are affected, rinse them for 10 minutes with plenty of water. If symptoms persist, seek medical treatment. Avoid inhaling electrolyte vapor or mists. Workplaces and other affected areas should be well ventilated. Clothing that has been contaminated by electrolyte must be changed and rinsed in water.



## Product safety

The table below summarizes the safety instructions that must be observed without fail. A detailed description can be found in the relevant sections of chapter "General technical information".


Topic	Safety information	Reference chapter "General technical information"
Polarity	Make sure that polar capacitors are connected with the right polarity.	1 "Basic construction of aluminum electrolytic capacitors"
Reverse voltage	Voltages polarity classes should be prevented by connecting a diode.	3.1.6 "Reverse voltage"
Mounting position of screw-terminal capacitors	Do not mount the capacitor with the terminals (safety vent) upside down.	11.1. "Mounting positions of capacitors with screw terminals"
Robustness of terminals	The following maximum tightening torques must not be exceeded when connecting screw terminals: M5: 2.5 Nm M6: 4.0 Nm	11.3 "Mounting torques"
Mounting of single-ended capacitors	The internal structure of single-ended capacitors might be damaged if excessive force is applied to the lead wires. Avoid any compressive, tensile or flexural stress. Do not move the capacitor after soldering to PC board. Do not pick up the PC board by the soldered capacitor. Do not insert the capacitor on the PC board with a hole space different to the lead space specified.	11.4 "Mounting considerations for single-ended capacitors"
Soldering	Do not exceed the specified time or temperature limits during soldering.	11.5 "Soldering"
Soldering, cleaning agents	Do not allow halogenated hydrocarbons to come into contact with aluminum electrolytic capacitors.	11.6 "Cleaning agents"
Upper category temperature	Do not exceed the upper category temperature.	7.2 "Maximum permissible operating temperature"
Passive flammability	Avoid external energy, such as fire or electricity.	8.1 "Passive flammability"



B41692, B41792


Compact – up to 140 °C

Topic	Safety information	Reference chapter "General technical information"
Active flammability	Avoid overload of the capacitors.	8.2 "Active flammability"
Maintenance	Make periodic inspections of the capacitors. Before the inspection, make sure that the power supply is turned off and carefully discharge the electricity of the capacitors. Do not apply any mechanical stress to the capacitor terminals.	10 "Maintenance"
Storage	Do not store capacitors at high temperatures or high humidity. Capacitors should be stored at +5 to +35 °C and a relative humidity of ≤ 75%.	7.3 Storage conditions
Breakdown strength of insulating sleeves	Do not damage the insulating sleeve, especially when ring clips are used for mounting.	Reference chapter "Capacitors with screw terminals"
		"Screw terminals – accessories"



## Symbols and terms

Symbol	English	German
C	Capacitance	Kapazität
$C_R$	Rated capacitance	Nennkapazität
$C_S$	Series capacitance	Serienkapazität
$C_{S,T}$	Series capacitance at temperature T	Serienkapazität bei Temperatur T
$C_f$	Capacitance at frequency f	Kapazität bei Frequenz f
d	Case diameter, nominal dimension	Gehäusedurchmesser, Nennmaß
$d_{\max}$	Maximum case diameter	Maximaler Gehäusedurchmesser
ESL	Self-inductance	Eigeninduktivität
ESR	Equivalent series resistance	Ersatzserienwiderstand
$ESR_f$	Equivalent series resistance at frequency f	Ersatzserienwiderstand bei Frequenz f
$ESR_T$	Equivalent series resistance at temperature T	Ersatzserienwiderstand bei Temperatur T
f	Frequency	Frequenz
I	Current	Strom
$I_{AC}$	Alternating current (ripple current)	Wechselstrom
$I_{AC,rms}$	Root-mean-square value of alternating current	Wechselstrom, Effektivwert
$I_{AC,f}$	Ripple current at frequency f	Wechselstrom bei Frequenz f
$I_{AC,max}$	Maximum permissible ripple current	Maximal zulässiger Wechselstrom
$I_{AC,R}$	Rated ripple current	Nennwechselstrom
$I_{AC,R}$ (B)	Rated ripple current for base cooling	Nennwechselstromstrom für Bodenkühlung
$I_{\text{leak}}$	Leakage current	Reststrom
$I_{\text{leak,op}}$	Operating leakage current	Betriebsreststrom
l	Case length, nominal dimension	Gehäselänge, Nennmaß
$l_{\max}$	Maximum case length (without terminals and mounting stud)	Maximale Gehäselänge (ohne Anschlüsse und Gewindegöhlen)
R	Resistance	Widerstand
$R_{\text{ins}}$	Insulation resistance	Isolationswiderstand
$R_{\text{symm}}$	Balancing resistance	Symmetrierwiderstand
T	Temperature	Temperatur
$\Delta T$	Temperature difference	Temperaturdifferenz
$T_A$	Ambient temperature	Umgebungstemperatur
$T_C$	Case temperature	Gehäsetemperatur
$T_B$	Capacitor base temperature	Temperatur des Becherbodens
t	Time	Zeit
$\Delta t$	Period	Zeitraum
$t_b$	Service life (operating hours)	Brauchbarkeitsdauer (Betriebszeit)



B41692, B41792

Compact – up to 140 °C

Symbol	English	German
V	Voltage	Spannung
$V_F$	Forming voltage	Formierspannung
$V_{op}$	Operating voltage	Betriebsspannung
$V_R$	Rated voltage, DC voltage	Nennspannung, Gleichspannung
$V_s$	Surge voltage	Spitzenspannung
$X_C$	Capacitive reactance	Kapazitiver Blindwiderstand
$X_L$	Inductive reactance	Induktiver Blindwiderstand
Z	Impedance	Scheinwiderstand
$Z_T$	Impedance at temperature T	Scheinwiderstand bei Temperatur T
$\tan \delta$	Dissipation factor	Verlustfaktor
$\lambda$	Failure rate	Ausfallrate
$\epsilon_0$	Absolute permittivity	Elektrische Feldkonstante
$\epsilon_r$	Relative permittivity	Dielektrizitätszahl
$\omega$	Angular velocity; $2 \cdot \pi \cdot f$	Kreisfrequenz; $2 \cdot \pi \cdot f$

### Note

All dimensions are given in mm.

## Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet ([www.epcos.com/material](http://www.epcos.com/material)). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CeraLink, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, FilterCap, FormFit, MiniBlue, MiniCell, MKD, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at [www.epcos.com/trademarks](http://www.epcos.com/trademarks).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## EPCOS:

[B41692A5687Q007](#) [B41692A5338Q007](#) [B41692A7477Q007](#) [B41692A7687Q007](#) [B41692A7108Q007](#)  
[B41692A7158Q007](#) [B41692B7158Q007](#) [B41692A7228Q007](#) [B41692A8227Q007](#) [B41692A8337Q007](#)  
[B41692A8477Q007](#) [B41692A8687Q007](#) [B41692B8687Q007](#) [B41692A5158Q009](#) [B41692A7687Q009](#)  
[B41692A8227Q009](#) [B41692A8337Q009](#) [B41692A8477Q009](#)

## EPCOS / TDK:

[B41692A5108Q007](#) [B41692A5228Q007](#) [B41692B5228Q007](#) [B41692A5608Q007](#) [B41692A7408Q007](#)  
[B41692A8108Q007](#) [B41692A8158Q007](#) [B41692A7108Q009](#) [B41792A5687Q000](#) [B41792A5158Q000](#)  
[B41792A5228Q000](#) [B41792A5338Q000](#) [B41792A7477Q000](#) [B41792A7687Q000](#) [B41792A7158Q000](#)  
[B41792A8337Q000](#)