








FCIconnect.com

Copyright FCI



Part Number & Date Code Printing
PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



Pull Parts							
SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	G±0.25	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	5.90	D09P13A*PA00**
15	39.14	33.32	25.18	25.12	19.18	5.90	D15P13A*PA00**
25	53.03	47.04	39.12	38.84	33.12	5.70	D25P13A*PA00**
37	69.32	63.50	55.68	55.30	49.68	5.70	D37P13A*PA00**

4-200 Mating cycles
6-500 Mating cycles

LF FOR LEAD FREE

GENERAL CHARACTERISTICS : SEE DRAWING C01-8646-0000

mat'l. code SEE NOTES				surface ISO 1302 ✓ tolerances unless otherwise specified			projection MM	product family D-SUB		
ltr	ecn no	dr	date	angles	linear	O.X ±0.1	scale 1:1	title		
D	[05-0124]	JS	2005/07/27			O.XX ±0.1		MALE CONNECT. DELTA D RIGHT ANGLED		
E	[06-0074]	SK	2006/06/08			O.XXX±0.1		SPILL WITHOUT ACCESSORIES		
F	ELXI-I-15060	AB	2013/06/25	X±1°				dwg no		
G	ELX-I-18884	AB	2014/09/24	dr	JOHN.SLEEBA	2004/08/04	FCI	sheet 1 of 1		
				engr	ALIAS.BABU	2014/09/24		C01-8646-0276		
				chr	MITHUN.PAUL	2014/09/24		A3		
				appd	BIJU.K.PAUL	2014/09/24		type PRODUCT_CUSTOMER Drawing		
sheet index	revision	G								
	sheet	1								