
[Products](#)
[Design Resources](#)
[Technical Info](#)
[Global Sales](#)
[---Useful Links---](#)

Quick Reference

Search by part #

 Check distributor
part inventory

Stock Check
[CLICK HERE!](#)

Products

Browse Products

Useful Links

[MSDS Safety Sheets](#)
[How to order?](#)
[Find Sales Rep](#)
[Find Distributor](#)
[Sample Request](#)
[Quote Request](#)
[Catalog Request](#)
[Building a part #](#)
[Part # Cross Ref](#)

Max Clip System™ Max Clips



The following Max Clips meet all requirements given:


MAX01

VIS Number: 032406

Force: 22.91 N [5.15 lbs]

Width: 9.9 mm [0.390 in]

Thickness: 0.51 mm [0.020 in]

Attachment: Max Clip Rail



MAX02

VIS Number: 032407

Force: 27.89 N [6.27 lbs]

Width: 11.9 mm [0.470 in]

Thickness: 0.51 mm [0.020 in]

Attachment: Max Clip Rail


MAX03

VIS Number: 032408

Force: 35.85 N [8.06 lbs]





Width: 15.0 mm [0.590 in]

Thickness: 0.51 mm [0.020 in]




Attachment: Max Clip Rail


MAX04

VIS Number: 032409	
Force: 47.82 N [10.75 lbs]	
Width: 20.1 mm [0.790 in]	
Thickness: 0.51 mm [0.020 in]	
Attachment: Max Clip Rail	
MAX09	
VIS Number: 032611	
Force: 44.84 N [10.08 lbs]	
Width: 9.9 mm [0.390 in]	
Thickness: 0.51 mm [0.020 in]	
Attachment: Max Clip Rail	
MAX10	
VIS Number: 032412	
Force: 39.85 N [8.96 lbs]	
Width: 11.9 mm [0.470 in]	
Thickness: 0.58 mm [0.023 in]	
Attachment: Max Clip Rail	
MAX11	
VIS Number: 032413	
Force: 39.85 N [8.96 lbs]	
Width: 11.9 mm [0.470 in]	
Thickness: 0.58 mm [0.023 in]	
Attachment: Max Clip Rail	
MAX12	
VIS Number: 032414	

Force: 24.91 N [5.60 lbs]	
Width: 6.0 mm [0.236 in]	
Thickness: 0.58 mm [0.023 in]	
Attachment: Max Clip Rail	
MAX13	
VIS Number: 032612	
Force: 39.85 N [8.96 lbs]	
Width: 17.0 mm [0.670 in]	
Thickness: 0.51 mm [0.020 in]	
Attachment: Max Clip Rail	
MAX14	
VIS Number: 032613	
Force: 19.93 N [4.48 lbs]	
Width: 13.0 mm [0.510 in]	
Thickness: 0.51 mm [0.020 in]	
Attachment: Max Clip Rail	
MAX15	
VIS Number: 032614	
Force: 59.78 N [13.44 lbs]	
Width: 18.0 mm [0.710 in]	
Thickness: 0.58 mm [0.023 in]	
Attachment: Max Clip Rail	
MAX16	
VIS Number: 032774	

Force: 39.85 N [8.96 lbs]	
Width: 17.0 mm [0.670 in]	
Thickness: 0.51 mm [0.020 in]	
Attachment: Max Clip Rail	
MAX17	
VIS Number: 032775	
Force: 19.93 N [4.48 lbs]	
Width: 13.0 mm [0.510 in]	
Thickness: 0.51 mm [0.020 in]	
Attachment: Max Clip Rail	
MAX20	
VIS Number: 032615	
Force: 49.82 N [11.20 lbs]	
Width: 11.9 mm [0.470 in]	
Thickness: 0.58 mm [0.023 in]	
Attachment: Max Clip Rail	
MAX23	
VIS Number: 032616	
Force: 72.72 N [16.35 lbs]	
Width: 18.0 mm [0.710 in]	
Thickness: 0.58 mm [0.023 in]	
Attachment: Max Clip Rail	
MAX01-H	
VIS Number: 032617	

Force: 59.78 N [13.44 lbs]	
Width: 9.9 mm [0.390 in]	
Thickness: 0.71 mm [0.028 in]	
Attachment: Max Clip Rail	
MAX02-H	
VIS Number: 032618	
Force: 49.82 N [11.20 lbs]	
Width: 13.0 mm [0.510 in]	
Thickness: 0.58 mm [0.023 in]	
Attachment: Max Clip Rail	
MAX03-H	
VIS Number: 032619	
Force: 59.78 N [13.44 lbs]	
Width: 18.0 mm [0.710 in]	
Thickness: 0.58 mm [0.023 in]	
Attachment: Max Clip Rail	