




- 1 0.38 μ m [$.000015$] MIN GOLD ON MATING AREA,
1.27 μ m [$.000050$] MIN BRIGHT TIN-LEAD ON CRIMP AREA, BOTH OVER
1.27 μ m [$.000050$] MIN NICKEL.
- 2 2.54 μ m [$.000100$] MIN BRIGHT TIN-LEAD, OVER
1.27 μ m [$.000050$] MIN NICKEL.
- 3 GOLD FLASH ON CRIMP AREA,
2.54 μ m [$.000100$] MIN TIN ON MATING AREA, BOTH OVER
1.27 μ m [$.000050$] MIN NICKEL.
- 4 0.38 μ m [$.000015$] MIN GOLD ON MATING AREA,
GOLD FLASH ON CRIMP AREA, BOTH OVER
1.27 μ m [$.000050$] MIN NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 6 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL

5 OBSOLETE	4	487923-5
3 6		487923-4
5 OBSOLETE	1	487923-3
2		487923-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 3-7-90	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK R.STONE 3-8-90			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
	0 PLC $\pm$ -		CONTACT, SOLDER TAB,		
	1 PLC $\pm$ -		.050 C/L		
	2 PLC $\pm$ 0.13 [$.005$]		-		
	3 PLC $\pm$ -		SIZE		
	4 PLC $\pm$ -		CAGE CODE		
	ANGLES $\pm$ -		DRAWING NO		
	FINISH		RESTRICTED TO		
MATERIAL		WEIGHT	A2 00779 C=487923		
PHOSPHOR BRONZE		SEE TABLE	-		
		CUSTOMER DRAWING	SCALE 10:1 SHEET 1 OF 1 REV D1		