

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0929031311](#)
Status: **Obsolete**
Description: LaneLink™/ InfiniBand* Direct Attach Cable Assembly, 4X, 28AWG, Latches, 2.0m (6.56') Length

Documents:
[Drawing \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	92903
Connector to Connector	InfiniBand* 4x Both Ends
More Detailed Tech Information	LaneLink™/ InfiniBand* Direct Attach Cable Assembly, 4X, 28AWG, Latches, 2m
Product Name	4X, InfiniBand*, LaneLink™
Physical	
Cable Length	2.0m (6.56')
Circuits (Loaded)	4X
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, Polyester, PVC
Packaging Type	Bag
Pitch - Mating Interface	0.50mm (.020")
Plating min - Mating	1.016µm (40µ")
Plating min - Termination	3.048µm (120µ")
Single Ended	No
Termination Interface: Style	IDT or Pierce, Solder or Weld, Surface Mount
Wire Size AWG	28
Wire/Cable Type	Parallel Pair

Electrical	
Current - Maximum per Contact	0.5A
Impedance	100#
Shielded	Yes
Voltage - Maximum	30V AC

Material Info

Reference - Drawing Numbers	
Packaging Specification	PK-92903-001
Product Specification	PS-91525-001
Sales Drawing	SD-92903-001

*InfiniBand is a trademark of the InfiniBand Trade Association

EU RoHS
Not RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[92903Series](#)

Mates With
[91525](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION