




87654321

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

1

MATERIAL:
CONTACT: PHOSPHOR BRONZE.
HOUSING: GLASS-FILLED POLYESTER.

2

GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1.27µm MIN NICKEL AND ACTION
PIN: 0.5µm MIN TIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.

3

CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 2.

4

CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 1.

5

CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,
CENTRAL OFFICE APPLICATIONS.

6

CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,
UNCONTROLLED ENVIROMENT APPLICATIONS.

7

CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.
ADDITIONAL CHARACTERS OR MARKINGS, AS WELL AS THE LOCATION OF THE MARKINGS,
MAY BE ADDED FOR TRACEABILITY BASED UPON MANUFACTURERS DISCRETION.

8

PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
PATTERN DEFINED BY CONTACT LAYOUT.

9

FOR ACTUAL PIN LOADING SEE "CONTACT LAYOUT".

10

FOR ACTUAL PIN DIMENSIONS SEE "CONTACT DIMENSIONS".

11

TO BE MEASURED AT BOTTOM OF SHROUD.

12

CONNECTOR LUBRICATED WITH BELCORE APPROVED LUBRICANT,
TECHNICAL REFERENCE: TR-NWT-001217 ISSUE 1, SEP 1992.

LOCAD

DIST00

REV

DESCRIPTION

DATE

DWN

APVD

—

SEE SHEET 1

—

—

—

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWNB CARBO29JUL05

CHKG SKIPPER29JUL05

APVGG SKIPPER29JUL05

DIMENSIONS:
mm

0-PLG±

1-PLG±0.1


2-PLG±

3-PLG±

4-PLG±

ANGLES

±0.2



APPLICATION SPEC
114-19029

WEIGHT—

MATERIAL
SEE SHEET 1

FINISH
SEE SHEET 1

SIZEA1

CAGE CODE00779

DRAWING NOG=5646533

RESTRICTED TO—

CUSTOMER DRAWING

SCALE4:1

SHEET2

OF2

REV A

Tyco Electronics

Tyco Electronics Corporation
Harriaburg, Pa 17105-3608

NAME

MALE ASSEMBLY, Z-PACK 2mm HM,
TYPE A/B