





| REV. | DATE     | ECR NO. | DESCRIPTION                    |
|------|----------|---------|--------------------------------|
| A    | 07/21/98 | —       | REDIMENSION AND ADD NOTES      |
| B    | 05/19/03 | —       | UPDATE DRAWING FORMAT          |
| C    | 02/10/04 | —       | MODIFY PLATING SPECS           |
| D    | 09/30/05 | —       | REVISE ALL PLATING TO BRT. TIN |
| E    | 11/14/05 | —       | UPDATE COMPONENT DIMENSIONS    |
| F    | 12/09/08 | 100063  | REVISE PLATING TO NICKEL       |



RECOMMENDED  
CABLE STRIPPING DIM'S



NOTE:  
1. CRIMPED FERRULE HEX CRIMP SIZE .128" [3.25]

|   |             |          |         |     |                                                                                                                                        |           |                   |          |  |                                                                  |                        |   |      |   |       |    |
|---|-------------|----------|---------|-----|----------------------------------------------------------------------------------------------------------------------------------------|-----------|-------------------|----------|--|------------------------------------------------------------------|------------------------|---|------|---|-------|----|
|   |             |          |         |     | UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.             | APPROVALS |                   | DATE     |  | Amphenol Connex                                                  |                        |   |      |   |       |    |
| 8 |             |          |         |     |                                                                                                                                        | DRAWN     | GRS               | 12/09/08 |  |                                                                  |                        |   |      |   |       |    |
| 7 |             |          |         |     |                                                                                                                                        | CHECKED   |                   |          |  | PART DESCRIPTION<br><br>F CRIMP PLUG<br>(RG-179/U CABLE – 75ohm) |                        |   |      |   |       |    |
| 6 |             |          |         |     |                                                                                                                                        | ISSUED    |                   |          |  |                                                                  |                        |   |      |   |       |    |
| 5 | FERRULE     | COPPER   | NICKEL  | 1   | UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:<br>0.5 – 8mm ± 0.20mm<br>8 – 30mm ± 0.40mm<br>30 – 120mm ± 0.50mm           | SHEET     | 1 OF 1            |          |  |                                                                  | PART NO.<br><br>222113 |   |      |   |       |    |
| 4 | RING        | BRASS    | NICKEL  | 1   | UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:<br>.020 – .315 = ± 0.007”<br>.315 – 1.180 = ± 0.015”<br>1.180 – 4.724 = ± 0.020” |           |                   |          |  |                                                                  |                        |   |      |   |       |    |
| 3 | CONTACT PIN | BRASS    | GOLD    | 1   |                                                                                                                                        |           |                   |          |  |                                                                  | DWG. NO. 222113.DWG    |   |      |   |       |    |
| 2 | DIELECTRIC  | PTFE     | NATURAL | 1   |                                                                                                                                        |           |                   |          |  |                                                                  | REV.                   | F | SIZE | A | SCALE | NA |
| 1 | BODY        | BRASS    | NICKEL  | 1   |                                                                                                                                        |           |                   |          |  |                                                                  |                        |   |      |   |       |    |
|   | DESCRIPTION | MATERIAL | FINISH  | QTY | DO NOT SCALE DRAWING                                                                                                                   |           | C:/222/222113.DWG |          |  |                                                                  |                        |   |      |   |       |    |