

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	00		C1	REVISED PER ECO-09-024927	09NOV09	KK	AEG


1. MATERIAL:
HOUSING – NYLON, BLACK, UL 94V-0.
OVERMOLDED TERMINAL ARRAY – PBT, BROWN.
TERMINALS – 0.33[.013] THICK PHOS BRONZE
PLATED WITH 1.27 μ m[.000050] MINIMUM HARD
GOLD IN LOCALIZED AREA AND 3.81 μ m[.000150]
MINIMUM MATTE TIN IN SOLDER AREA OVER 1.27 μ m
[.000050] MINIMUM NICKEL UNDERPLATE.
SHIELD – 0.254[.010] THICK COPPER ALLOY PLATED
WITH 1.27 μ m[.000050] MINIMUM NICKEL AND
2.03 μ m[.000080] MINIMUM HOT TIN DIP ON PCB
GROUND TABS.
- 2

JACK CAVITY CONFORMS TO FCC RULES AND
REGULATIONS, PART 68 SUBPART F.
- 3

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI

(A)	(B)	(C)	ALL THREE	5406275-3
	(B)		(1) MIDDLE	5406275-2
	NONE		NONE	-5406275-1
HOLES USED			NO. OF REAR TABS	PART NO.

SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE (TOP)
SCALE 4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA – 07JUN2005	 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [inches]		CHK J. WESTMAN 07JUN2005		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.25[.01] 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-1163-2	
	FINISH		APPLICATION SPEC 114-2048	
MATERIAL SEE NOTE 1		WEIGHT -	SIZE A2	
SEE NOTE 1		CUSTOMER DRAWING		RESTRICTED TO -
SCALE 2:1			SHEET 1 OF 1	REV C1