




This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

**Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.**

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



SPECIFICATIONS

TUSONIX STYLE:	2425-527
CAP. VALUE:	5000 pF
CAP. TOLERANCE:	+80%, -20%
TEMP. CHARACTERISTIC:	X5W
RATING:	200 VDC @ + 85°C/100 VDC @ +125°C
OPERATING RANGE:	-55°C TO +125°C
IR MIN. @ 100 VDC:	10 G Ω
DWV VDC:	600

- NOTES:**
1. SUPPLIED WITH SILVER PLATED HEX NUT.
 2. TUSONIX STANDARD PART NUMBER: 2425-527-X5W0-502Z. TUSONIX RoHS COMPLIANT PART NUMBER: 2425-527-X5W0-502Z LF. CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
 3. PART MARKING: STANDARD PART: BLACK INK FOR TRADEMARK AND CAP. CODE. RoHS PART: GREEN INK FOR TRADEMARK AND CAP. CODE.

REVISION RECORD Original Release C.O. ECO-878	A		--TOLERANCES-- Unless Otherwise Specified	Title MINIATURE BUSHING FEED-THRU CAPACITOR	
			DECIMAL ± .031 [0.79]	Drawn L.E. 07-30-09	
			ANGLES ±	Approved R.L. 07-30-09	
			TUSONIX TUCSON, ARIZONA	A 2425-527-X5W0-502Z	