






变更为铆压结构



NOTES:
1.ELECTRONIC:
CONTACT RESISTANCE: 30mohm MAX
INSULATION RESISTANCE: 100 Mohm MIN
WITHSTAND VOLTAGE:AC 100V,1min.
2.MECHANICAL:
DURABILITY: 1500 CYCLE.
P.C.B ENVIRONMENT CHARACTERISTICS:
OPERATING TEMPERATURE:-25°C TO +85°C



RECOMMENDED P.C.B
LAYOUT(1.0~1.60±0.05)

Pin #	SIGNAL NAME	DESCRIPTION	MATING SEQUENCE
1	VBUS	POWER	THIRD
2	D-	USB 2.0 DIFFERENTIAL PAIR	THIRD
3	D+	DIFFERENTIAL PAIR	THIRD
4	GND	GROUND FOR POWER RETURN	SECOND
5	Stda_SSRx+	SUPERSPEED RECEIVER	LAST
6	Stda_SSRx+	DIFFERENTIAL PAIR	LAST
7	GND_DRAIN	GROUND FOR SIGNAL RETURN	LAST
8	Stda_SSTx-	SUPERSPEED TRANSMITTER	LAST
9	Stda_SSTx+	DIFFERENTIAL PAIR	LAST
Shell	Shield	CONNECTOR METAL SHELL	FRIST

3	SHELL	1	C2680	NI PLATED
2	CONTACT	9	C2680	AU/TIN PLATED
1	HOUSING	1	LCP	<UL 94V-0> BLUE
No.	PART NAME	QTY	MATERIAL	REMARK

CnC Tech, LLC

-TOLERANCES-		TITLE: USB 3.0 AF 沉板SMT 卷边方脚	
UNLESS OTHERWISE SPECIFIED		DATE	
X.X	± 0.25	X.X°	± 3.00°
X.XX	± 0.20	X.XX°	± 1.00°
X.XXX	± 0.15	X.XXX°	± 0.500°

APPD:	PRODUCT NO:	1003-002-01100
CHECK:	DATE	2012/04/06
DRAW:	SCALE	1:1
	UNIT	mm
	TYPE	Z
	PAGE	1 / 1