


# High Density D-Sub Connectors Male

156-1815-E, 156-1826-E



High Density D-Sub Connectors Male



Dimensions: mm (in.)

| Mouser Stock No. | No. of pins | A     | B     | C    | D    | E    | F    |
|------------------|-------------|-------|-------|------|------|------|------|
| 156-1815-E       | 15          | 16.92 | 25.00 | 30.8 | 2.29 | 1.14 | 19.2 |
| 156-1826-E       | 26          | 25.25 | 33.30 | 39.2 | 2.29 | 1.14 | 27.7 |

| SPECIFICATIONS                   |                                              |
|----------------------------------|----------------------------------------------|
| Contact current rating:          | 3 amperes                                    |
| Contact resistance:              | 15 MΩ Max. @ 500VDC                          |
| Operating temperature:           | -55°C to +105°C                              |
| Dielectric withstanding voltage: | 1000 VAC/Minute.                             |
| Insulator                        | Thermal Plastic                              |
| Contacts                         | Copper Alloy                                 |
| Shell                            | Steel                                        |
| Rivet, Boardlock                 | Copper Alloy                                 |
| Underplate                       | 50μ" Nickel                                  |
| Contact Area                     | 1μ"~30μ" Selective Gold                      |
| Solder Tails                     | 100μ" Tin/Lead Free (Brighten Tin/Matte Tin) |
| RoHS Compliant                   |                                              |

Date Last Revised: 6-13-12

Available from Mouser Electronics  
1-800-346-6873 / [www.mouser.com](http://www.mouser.com)

KC- 301144

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

156-1815-E, 156-1826-E

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[156-1826-E](#) [156-1815-E](#)