


Stud Type Block

Altech DIN rail mounting Stud Type Terminal Blocks are preferred for the connections that are subjected to very severe vibrations.


The wire is crimped to a ring / fork type lug and is screwed on to the flat current bar in terminal. The range includes terminal blocks for wires of size 22-4 AWG.

Jumpering can be achieved with the aid of external jumpers. The jumpers are insulated to make them shock proof. The terminal blocks have marker holding recess to accommodate MT type marking tags.


It is recommended to use protective covers in transparent plastic because assemblies of these terminals blocks are not fully covered.



CSTSN4U



CSTSN5U



Terminal Width	17 mm			17 mm		
Height x Length	39.5 x 50 mm			39.5 x 50 mm		
Stripping Length	12 mm			12 mm		
Insulation Material	Polyamide 6.6			Polyamide 6.6		
Type of Connection	2 screw connection for M4 ring/fork lugs			2 screw connection for M5 ring/fork lugs		
Approvals						
Wire Range	22-6 AWG	1.5-10 sq.mm	22-6 AWG	22-4 AWG	1.5-16 sq.mm	22-4 AWG
Voltage Rating	600 V	800 V	600 V	600 V	800 V	600 V
Current Rating	65 A	57 A	65 A	80 A	76 A	80 A
Torque	14 lb-in	1.2 Nm	14 lb-in	17.5 lb-in	2.0 Nm	17.5 lb-in
Other Approvals						

Terminal Block

End Plate	
-----------	---

DIN Rail
for ordering information
refer to page 70

End Stop for ordering information refer to page 72	
--	---

Protective Cover for covering	 2 Terminal 3 Terminal
----------------------------------	--

Protective Cover in Length	 100 mm 200 mm 300 mm
-------------------------------	--

Insulated Removable Jumpers	 2 way 3 way 4 way
--------------------------------	---

Insulated Permanent Jumpers	 2 way 3 way 4 way
--------------------------------	---

Marking Tags (MT Type)	
------------------------	---

Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
CSTSN4U	100	CSTSN5U	100
EPCSTSN5U	50	EPCSTSN5U	50
			
CA702	50	CA702	50
CA802	50	CA802	50
CSTSPC1	100	CSTSPC1	100
CSTSPC1-1	100	CSTSPC1-1	100
CSTSPC1-2	10	CSTSPC1-2	10
CSTSPC1-3	10	CSTSPC1-3	10
CSTSPC1-4	10	CSTSPC1-4	10
CA514/1-2	100	CA514/1-2	100
CA514/1-3	50	CA514/1-3	50
CA514/1-4	50	CA514/1-4	50
CA514/3-2	100	CA514/3-2	100
CA514/3-3	50	CA514/3-3	50
CA514/3-4	50	CA514/3-4	50
MT2	100	MT2	100

COLOR BLOCKS

(other than grey standard)

When ordering please add
color suffix to Cat. No.

Example: CTS2.5U-N/R

Color	Ordering Suffix
Red	R
Blue	BU
Black	BL
Orange	O
Green	G
Yellow	Y
White	W
Beige	BG
Dark Brown	DB

CSTSB4U

CSTSB5U


Terminal Width	17 mm			17 mm		
Height x Length	39.5 x 50 mm			39.5 x 50 mm		
Stripping Length	12 mm			12 mm		
Insulation Material	Polyamide 6.6			Polyamide 6.6		
Type of Connection	2 screw connection for M4 ring/fork lugs			2 screw connection for M5 ring/fork lugs		
Approvals						
Wire Range	22-6 AWG	1.5-10 sq.mm	22-6 AWG	22-4 AWG	1.5-16 sq.mm	22-4 AWG
Voltage Rating	600 V	800 V	600 V	600 V	800 V	600 V
Current Rating	65 A	57 A	65 A	80 A	76 A	80 A
Torque	14 lb-in	1.2 Nm	14 lb-in	17.5 lb-in	2.0 Nm	17.5 lb-in
Other Approvals						

Terminal Block

End Plate


DIN Rail
for ordering information
refer to page 70

End Stop
for ordering information
refer to page 72

Protective Cover
for covering

2 Terminal
3 Terminal

Protective Cover
in Length

100 mm
200 mm
300 mm

Insulated Removable
Jumpers

2 way
3 way
4 way

Insulated Permanent
Jumpers

2 way
3 way
4 way

Marking Tags (MT Type)



Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
CSTSB4U	100	CSTSB5U	100
EPCSTN5U	50	EPCSTN5U	50
CA702	50	CA702	50
CA802	50	CA802	50
CSTSPC1	100	CSTSPC1	100
CSTSPC1-1	100	CSTSPC1-1	100
CSTSPC1-2	10	CSTSPC1-2	10
CSTSPC1-3	10	CSTSPC1-3	10
CSTSPC1-4	10	CSTSPC1-4	10
CA514/1-2	100	CA514/1-2	100
CA514/1-3	50	CA514/1-3	50
CA514/1-4	50	CA514/1-4	50
CA514/3-2	100	CA514/3-2	100
CA514/3-3	50	CA514/3-3	50
CA514/3-4	50	CA514/3-4	50
MT2	100	MT2	100