








REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
	C	REVISED PER ECR-16-005516	25APR2016	DLD	CJS



- △ MATERIAL: COPPER ALLOY.
- △ FINISH: PRE-PLATED WITH 1.00µm MIN BRIGHT TIN.
- △ MATERIAL ID FEATURE IN "DOWN" POSITION.
- 4. THE INTENDED TEMPERATURE RANGE FOR THIS TERMINAL IS -40°C TO +100°C.
- 5. TERMINAL HAS NYE LUBRICANTS NYETACT 568J-50-UV PERFORMANCE LUBE/GREASE APPLIED. THIS IS A WHITISH COLORED LUBE. AMOUNT AND VISIBILITY MAY VARY.
- △ NOT FOR SEALED APPLICATIONS.
- △ SEALING CAPABILITY MUST BE VALIDATED ON AN APPLICATION BASIS.



0.13mm ² = 0.85-1.05	DETAIL B	1.40	2.40	0.80	1.85	△ 2 △ 3	2X 0.13mm ² △ 6	2035334-8
0.35mm ² = 1.10-1.40							0.35mm ² △ 7	
0.85-1.05	DETAIL B	0.85	1.82	0.65	1.50	△ 2 △ 3	26 [0.13mm ²]	2035334-7 △ 6
0.13mm ² = 0.85-1.05	DETAIL A	1.40	2.40	0.80	1.85	△ 2 △ 3	2X 0.13mm ² △ 6	2035334-6
0.35mm ² = 1.10-1.40							0.35mm ² △ 7	
0.85-1.05	DETAIL A	0.85	1.82	0.65	1.50	△ 2 △ 3	26 [0.13mm ²]	2035334-5 △ 6
2.06 MAX	DETAIL B	1.78	2.94	1.00	1.96	△ 2 △ 3	18 [0.75mm ²]	2035334-4
1.50-1.85	DETAIL B	1.78	2.94	0.80	1.82	△ 2 △ 3	20-22 [0.5-0.35mm ²]	2035334-3
2.06 MAX	DETAIL A	1.78	2.94	1.00	1.96	△ 2 △ 3	18 [0.75mm ²]	2035334-2
1.50-1.85	DETAIL A	1.78	2.94	0.80	1.82	△ 2 △ 3	20-22 [0.5-0.35mm ²]	2035334-1
INSULATION DIAMETER	REELING	M	L	K	J	FINISH	WIRE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
R. VESTAL

CHK
C. SCHMID

APVD
C. SCHMID

01JUL2008
01JUL2008
01JUL2008

DIMENSIONS:

mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.15
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

±
±
±
±
±
±
-

PRODUCT SPEC

108-2296

APPLICATION SPEC

114-13183

WEIGHT

-

CUSTOMER DRAWING

NAME

CONTACT, FEMALE, 0.64, GENERATION Y SEALED APPLICATIONS

SIZE

CAGE CODE

DRAWING NO

2035334

SCALE

15:1

SHEET

1

OF

1

REV

C

TE Connectivity

RESTRICTED TO

-