





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		E	REVISED PER ECO-12-007964	02MAY2012	KH	MS



- 1
- MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.
- 2
- SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
OBSOLETE
- 3
- RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC.FILE N° E60677.
- 4
- IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.
- 5
- NOT CUMULATIVE TOLERANCE.




282818-2 AS SHOWN



OBSOLETE	128.82 ^{+0.40} _{-0.25}	13	1-282818-3
	118.66 ^{+0.40} _{-0.25}	12	1-282818-2
OBSOLETE	108.50 ^{+0.40} _{-0.25}	11	1-282818-1
OBSOLETE	98.34 ^{+0.40} _{-0.25}	10	1-282818-0
	88.18 ^{+0.35} _{-0.25}	9	282818-9
	78.02 ^{+0.35} _{-0.25}	8	282818-8
	67.86 ^{+0.35} _{-0.20}	7	282818-7
OBSOLETE	57.70 ^{+0.30} _{-0.20}	6	282818-6
	47.54 ^{+0.30} _{-0.20}	5	282818-5
	37.38 ^{+0.25} _{-0.10}	4	282818-4
	27.22 ^{+0.25} _{-0.10}	3	282818-3
	17.06 ^{+0.20} _{-0.10}	2	282818-2
DIM. A		N° OF POS.	PART NUMBER

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.2

1 PLC ±.2

2 PLC ±.25

3 PLC ±.25

4 PLC ±.25

ANGLES ±.2

FINISH

DWN E. ZANOLINI 26 JUL 2001

CHK D. BIEVENOUR 26 JUL 2001

APVD D. BIEVENOUR 26 JUL 2001

PRODUCT SPEC 108-20166

APPLICATION SPEC 114-20079

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL BLOCK HEADER ASSEMBLY
90 DEG CLOSED ENDS
10.16mm PITCH

SIZE A3 CAGE CODE 00779 DRAWING NO C-282818

RESTRICTED TO -

SCALE 3:1 SHEET 1 OF 1 REV E