





I.D.C SOCKET DUAL-ROW SR




MATERIALS:
INSULATOR: P.B.T. 30% GLASS FIBER, UL94V-0
CONTACT MATERIAL: BRASS OR PHOSPHOR BRONZE,
GOLD FLASH OVER NICKEL

ELECTRICAL:
CURRENT RATING: 1AMP.
INSULATION RESISTANCE: 1000MΩ MIN.
DIELECTRIC WITHSTANDING: 500VAC
OPERATING TEMPERATURE: -55°C ~ +105°C

AWP2-XX-7240-R

Number of Contacts

10/14/16/20/26/34/40/44/50



UNLESS OTHERWISE SPECIFIED TOLERANCE		ASSMANN Electronic Components	
ANG.	±5°	DRAWN NAME: J.D.C. SOCKET DUAL-ROW PITCH: 2.0mm PRODUCT NO. AWP2-XX-7240-R FILE NAME:	
.0	±0.5		
.00	±0.3		
.000	±0.2		
SCALE: AS SHOWN	UNIT: mm	DRAWN: TERRY 10/07/05	
CHECKED	Joe	10/07/05	
APPROVED	Mube	10/07/05	
DATE	10/07/05	REV. A	
SIZE	A4		

REV.	DESCRIPTION	DATE
A	ECN-0510053(Rita)	10/07/05