

Medium Power Thyristors (Stud Version), 50 A



TO-208AC (TO-65)

FEATURES

- High current rating
- Excellent dynamic characteristics
- $dV/dt = 1000 \text{ V}/\mu\text{s}$ option
- Superior surge capabilities
- Standard package
- Metric threads version available
- Types up to $1200 \text{ V } V_{\text{DRM}}/V_{\text{RRM}}$
- RoHS compliant



PRODUCT SUMMARY

$I_{\text{T(AV)}}$	50 A
--------------------	------

TYPICAL APPLICATIONS

- Phase control applications in converters
- Lighting circuits
- Battery charges
- Regulated power supplies and temperature and speed control circuit
- Can be supplied to meet stringent military, aerospace and other high reliability requirements

MAJOR RATINGS AND CHARACTERISTICS

PARAMETER	TEST CONDITIONS	VALUES	UNITS
$I_{\text{T(AV)}}$		50	A
	T_{C}	94	$^{\circ}\text{C}$
$I_{\text{T(RMS)}}$		80	A
I_{TSM}	50 Hz	1430	A
	60 Hz	1490	
I^2t	50 Hz	10.18	kA^2s
	60 Hz	9.30	
$V_{\text{DRM}}/V_{\text{RRM}}$		100 to 1200	V
t_{q}	Typical	110	μs
T_{J}		- 40 to 125	$^{\circ}\text{C}$

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS				
TYPE NUMBER	VOLTAGE CODE	V_{DRM}/V_{RRM} , MAXIMUM REPETITIVE PEAK AND OFF-STATE VOLTAGE ⁽¹⁾ V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK VOLTAGE ⁽²⁾ V	I_{DRM}/I_{RRM} MAXIMUM AT $T_J = T_J$ MAXIMUM mA
50RIA	10	100	150	15
	20	200	300	
	40	400	500	
	60	600	700	
	80	800	900	
	100	1000	1100	
	120	1200	1300	

Notes(1) Units may be broken over non-repetitively in the off-state direction without damage, if di/dt does not exceed 20 A/ μ s(2) For voltage pulses with $t_p \leq 5$ ms

ABSOLUTE MAXIMUM RATINGS						
PARAMETER	SYMBOL	TEST CONDITIONS			VALUES	UNITS
Maximum average on-state current at case temperature	I _{T(AV)}	180° sinusoidal conduction			50	A
					94	°C
Maximum RMS on-state current	I _{T(RMS)}				80	A
Maximum peak, one-cycle non-repetitive surge current	I _{TSM}	t = 10 ms	No voltage reapplied	Sinusoidal half wave, initial T _J = T _J maximum	1430	A
		t = 8.3 ms			1490	
		t = 10 ms	100 % V _{RRM} reapplied		1200	
		t = 8.3 ms			1255	
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reapplied		10.18	kA ² s
		t = 8.3 ms			9.30	
		t = 10 ms	100 % V _{RRM} reapplied		7.20	
		t = 8.3 ms			6.56	
Maximum I ² √t for fusing	I ² √t	t = 0.1 to 10 ms, no voltage reapplied, T _J = T _J maximum			101.8	kA ² √s
Low level value of threshold voltage	V _{T(TO)1}	(16.7 % × π × I _{T(AV)} < I < π × I _{T(AV)}), T _J = T _J maximum			0.94	V
High level value of threshold voltage	V _{T(TO)2}	(π × I _{T(AV)} < I < 20 × π × I _{T(AV)}), T _J = T _J maximum			1.08	
Low level value of on-state slope resistance	r _{t1}	(16.7 % × π × I _{T(AV)} < I < π × I _{T(AV)}), T _J = T _J maximum			4.08	mΩ
High level value of on-state slope resistance	r _{t2}	(π × I _{T(AV)} < I < 20 × π × I _{T(AV)}), T _J = T _J maximum			3.34	
Maximum on-state voltage	V _{TM}	I _{pk} = 157 A, T _J = 25 °C			1.60	V
Maximum holding current	I _H	T _J = 25 °C, anode supply 22 V, resistive load, initial I _T = 2 A			200	mA
Latching current	I _L	Anode supply 6 V, resistive load			400	



SWITCHING					
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum rate of rise of turned-on current	$V_{\text{DRM}} \leq 600 \text{ V}$	di/dt	$T_C = 125^\circ\text{C}$, $V_{\text{DM}} = \text{Rated } V_{\text{DRM}}$, Gate pulse = 20 V, 15 Ω , $t_p = 6 \mu\text{s}$, $t_r = 0.1 \mu\text{s}$ maximum $I_{\text{TM}} = (2 \times \text{rated } di/dt) \text{ A}$	200	A/ μs
	$V_{\text{DRM}} \leq 1600 \text{ V}$			100	
Typical delay time		t_d	$T_C = 25^\circ\text{C}$, $V_{\text{DM}} = \text{Rated } V_{\text{DRM}}$, $I_{\text{TM}} = 10 \text{ A}$ dc resistive circuit Gate pulse = 10 V, 15 Ω source, $t_p = 20 \mu\text{s}$	0.9	μs
Typical turn-off time		t_q	$T_C = 125^\circ\text{C}$, $I_{\text{TM}} = 50 \text{ A}$, reapplied $dV/dt = 20 \text{ V}/\mu\text{s}$ $dI_r/dt = -10 \text{ A}/\mu\text{s}$, $V_R = 50 \text{ V}$	110	

BLOCKING				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum critical rate of rise of off-state voltage	dV/dt	T _J = T _J maximum linear to 100 % rated V _{DRM}	200	V/μs
		T _J = T _J maximum linear to 67 % rated V _{DRM}	500 ⁽¹⁾	

Note

⁽¹⁾ Available with $dV/dt = 1000 \text{ V}/\mu\text{s}$, to complete code add S90 i.e. 50RIA120S90

TRIGGERING					
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum peak gate power		P_{GM}	$T_J = T_J$ maximum, $t_p \leq 5 \text{ ms}$	10	W
Maximum average gate power		$P_{\text{G(AV)}}$		2.5	
Maximum peak positive gate current		I_{GM}		2.5	A
Maximum peak positive gate voltage		$+V_{\text{GM}}$		20	V
Maximum peak negative gate voltage		$-V_{\text{GM}}$		10	
DC gate current required to trigger	I_{GT}	$T_J = -40^\circ\text{C}$	Maximum required gate trigger current/voltage are the lowest value which will trigger all units 6 V anode to cathode applied	250	mA
		$T_J = 25^\circ\text{C}$		100	
		$T_J = 125^\circ\text{C}$		50	
DC gate voltage required to trigger	V_{GT}	$T_J = -40^\circ\text{C}$		3.5	V
		$T_J = 25^\circ\text{C}$		2.5	
DC gate current not to trigger		I_{GD}	$T_J = T_J$ maximum, $V_{\text{DRM}} = \text{Rated voltage}$	5.0	mA
DC gate voltage not to trigger		V_{GD}	$T_J = T_J$ maximum	0.2	V

THERMAL AND MECHANICAL SPECIFICATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum operating junction and storage temperature range	T_J, T_{Stg}		- 40 to 125	°C
Maximum thermal resistance, junction to case	R_{thJC}	DC operation	0.35	K/W
Maximum thermal resistance, case to heatsink	R_{thCS}	Mounting surface, smooth, flat and greased	0.25	
Allowable mounting torque		Non-lubricated threads	$3.4 \pm 0.10\%$ (30)	N · m (lbf · in)
		Lubricated threads	$2.3 \pm 0.10\%$ (20)	
Approximate weight			28	g
			1.0	oz.
Case style		See dimensions - link at the end of datasheet	TO-208AC (TO-65)	

ΔR_{thJC} CONDUCTION				
CONDUCTION ANGLE	SINUSOIDAL CONDUCTION	RECTANGULAR CONDUCTION	TEST CONDITIONS	UNITS
180°	0.078	0.057	$T_J = T_J \text{ maximum}$	K/W
120°	0.094	0.098		
90°	0.120	0.130		
60°	0.176	0.183		
30°	0.294	0.296		

Note

- The table above shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 3 - On-State Power Loss Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 4 - On-State Power Loss Characteristics




Fig. 6 - Maximum Non-Repetitive Surge Current




Fig. 7 - Forward Voltage Drop Characteristics




Fig. 8 - Thermal Impedance Z_{thJC} Characteristics




Fig. 9 - Gate Characteristics

ORDERING INFORMATION TABLE

Device code	50	RIA	120	S90	M
	1	2	3	4	5

- 1** - Current code
- 2** - Essential part number
- 3** - Voltage code $\times 10 = V_{RRM}$ (see Voltage Ratings table)
- 4** - Critical dV/dt :
 - None = 500 V/ μ s (standard value)
 - S90 = 1000 V/ μ s (special selection)
- 5** -
 - None = Stud base TO-208AC (TO-65) 1/4" 28UNF-2A
 - M = Stud base TO-208AC (TO-65) M6 \times 1

LINKS TO RELATED DOCUMENTS	
Dimensions	http://www.vishay.com/doc?95334



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.