





LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			F2	REVISED PER ECR-12-008993	24MAY2012	KH	TM





- | | | | | |
|--|--|--|--|--|
| | | | | |
|--|--|--|--|--|

 - ① MATERIAL;
CONTACTS - BRASS.
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR; BLACK.
 - ② PLATING;
CONTACTS - 0.76 μ m MINIMUM GOLD OVER 2.54 μ m MINIMUM NICKEL
ON MATING AREA. 2.54 μ m TIN-LEAD MINIMUM OVER 2.54 μ m NICKEL
MINIMUM ON SOLDER TAILS.
HOLDDOWNS - 2.54 μ m TIN-LEAD.
 - ④ RECOMMENDED PC BOARD THICKNESS OF 1.57.
 - ⑤ PLATING;
CONTACTS - 0.76 μ m MINIMUM GOLD OVER 2.54 μ m MINIMUM NICKEL
ON MATING AREA. 2.54 μ m MATTE TIN MINIMUM OVER 2.54 μ m NICKEL
MINIMUM ON SOLDER TAILS.
HOLDDOWNS - 2.54 μ m MATTE TIN.
 - ⑥ CIRCUIT NUMBER 1 IS LOCATED AT THE BOTTOM RIGHT
WITH THE LATCH-LOCK ON TOP LOOKING INTO THE CAVITIES



	36.86	37.30	33.00	40.00	24	5-794679-4
	33.86	34.30	30.00	37.00	22	5-794679-2
	30.86	31.30	27.00	34.00	20	5-794679-0
	27.86	28.30	24.00	31.00	18	4-794679-8
	24.86	25.30	21.00	28.00	16	4-794679-6
	21.86	22.30	18.00	25.00	14	4-794679-4
	18.86	19.30	15.00	22.00	12	4-794679-2
	15.86	16.30	12.00	19.00	10	4-794679-0
	12.86	13.30	9.00	16.00	8	3-794679-8
	9.86	10.30	6.00	13.00	6	3-794679-6
	6.86	7.30	3.00	10.00	4	3-794679-4
	3.86	4.30	-	7.00	2	3-794679-2
	36.86	37.30	33.00	40.00	24	2-794679-4
	33.86	34.30	30.00	37.00	22	2-794679-2
	30.86	31.30	27.00	34.00	20	2-794679-0
	27.86	28.30	24.00	31.00	18	1-794679-8
	24.86	25.30	21.00	28.00	16	1-794679-6
	21.86	22.30	18.00	25.00	14	1-794679-4
	18.86	19.30	15.00	22.00	12	1-794679-2
	15.86	16.30	12.00	19.00	10	1-794679-0
	12.86	13.30	9.00	16.00	8	794679-8
	9.86	10.30	6.00	13.00	6	794679-6
	6.86	7.30	3.00	10.00	4	794679-4
	3.86	4.30	-	7.00	2	794679-2
FINISH	DIM Y	DIM W	DIM Z	DIM X	NO. OF POSN.	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B HAYMAKER	12AUG99	 TE Connectivity				
DIMENSIONS: mm		CHK K COBLE	12AUG99					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K COBLE 12AUG99	NAME THRU-HOLE, RIGHT ANGLE, 30 GOLD HEADER, MECHANICAL BOARDLOCK, DUAL ROW, MICRO MATE-N-LOK™				
	0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ±		PRODUCT SPEC -					
	ANGLES ±		APPLICATION SPEC -					
	FINISH		WEIGHT -					
MATERIAL 	SEE TABLE		CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779	DRAWING NO C-794679	RESTRICTED TO -
				SCALE 4:1	SHEET 1	OF 1	REV E2	