





RECOMMENDED P.C.B. LAYOUT





CIRCUIT: 2PDT

SWITCH FUNCTION	
PDS 1	PDS 2
DN	DN
2-1,5-4	2-3,5-6

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 0.1A @30V DC
5. TRAVEL: TRAVEL:=2.50±0.38
6. OPERATING FORCE:180±50gf
7. CONTACT RESISTANCE: 50mILLI-Ohms MAX. Initially
8. ELECTRICAL LIFE (at Full Load):
10,000 Cycles Make & Break
- ▲ 9. DESIGNATE MAJOR FEATURE:



TITLE			
TL2201 DA Y B (W/320.094 GRV)			
E-SWITCH®			
A	12609	RELEASED FOR PRODUCTION	12/4/02
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE			
2:1			
DATE			
12/4/02			
DR			
CB			
DWG			
XP02474			
REV			
A			