




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		J5	REVISED PER ECR-12-013486	06JAN13	KH	KR

SUGGESTED MATING TAB



- MATL: #2 HARD BRASS OR NICKEL PLATE STEEL.
 - NO BURRS PERMISSIBLE AT HOLE.
 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMPURTURE IS OVER 225° F.
 - MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
 - HOLE MUST BE SYMMETRICAL ABOUT TAB $\perp$ WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



VIEW A-A

SECTION B-B

SECTION C-C

GOLD / NICKEL $\triangle 7$	BRASS	$\triangle 8$ 63196-5
---	BRASS	63196-4
GOLD / NICKEL $\triangle 6$	BRASS	$\triangle 8$ 63196-3
PRE-TIN	BRASS	63196-2
TIN	BRASS	63196-1
FINISH	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN JR RUTH 2/28/87		 TE Connectivity												
			CHK G YETTER 3/9/87														
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R KUZO 3/9/87		NAME RECEPTACLE, POSITIVE LOCK, .187 SERIES —											
		0 PLC ± —		PRODUCT SPEC													
		1 PLC ± —		—													
		2 PLC ± —		APPLICATION SPEC													
		3 PLC ± 0.25 .010		—													
4 PLC ± —		ANGLES ± ±		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO					
MATERIAL		FINISH		WEIGHT —		A2		00779		C=63196		—					
SEE TABLE		SEE TABLE		CUSTOMER DRAWING		SCALE		5:1		SHEET		1 of 1		REV		J5	